



SITOP PSU3600 FLEXI/1AC/3-52VDC/10A/120W

SITOP PSU3600 flexi Stabilized power supply Input: 120-230 V AC Output: 3-52 V DC/10 A, 120 W

Input	
type of the power supply network	1-phase AC or DC
supply voltage at AC <ul style="list-style-type: none"> • minimum rated value • maximum rated value • initial value • full-scale value 	120 V 230 V 85 V; Derating at < 110 V AC/DC: output power max. 100 W 264 V
supply voltage <ul style="list-style-type: none"> • at DC 	110 ... 220 V
input voltage <ul style="list-style-type: none"> • at DC 	88 ... 250 V
design of input wide range input	Yes
operating condition of the mains buffering	With Pa = 120 W and Ue = 230 V AC
buffering time for rated value of the output current in the event of power failure minimum	80 ms
operating condition of the mains buffering	With Pa = 120 W and Ue = 230 V AC
line frequency <ul style="list-style-type: none"> • 1 rated value • 2 rated value 	50 Hz 60 Hz
line frequency	47 ... 63 Hz
input current <ul style="list-style-type: none"> • at rated input voltage 120 V • at rated input voltage 230 V • at rated input voltage 110 V • at rated input voltage 220 V 	2.6 A 1.3 A 1.3 A 0.7 A
current limitation of inrush current at 25 °C maximum	35 A
I ² t value maximum	1 A ² ·s
fuse protection type <ul style="list-style-type: none"> • in the feeder 	T 3.15 A (not accessible) Recommended miniature circuit breaker: 6-10 A characteristic C
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
formula for output voltage	3-52 V DC
output voltage <ul style="list-style-type: none"> • at output 1 at DC rated value 	24 V
relative overall tolerance of the voltage	1 %
relative control precision of the output voltage <ul style="list-style-type: none"> • on slow fluctuation of input voltage • on slow fluctuation of ohm loading 	0.1 % 1 %
voltage compensation per sense line	0.5 V

residual ripple	
• maximum	50 mV
voltage peak	
• maximum	100 mV
adjustable output voltage	0 ... 52 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer (setting range 3 to 52 V) or analog control voltage signal 0 to 2.5 V (setting range 0 to 52 V)
display version for normal operation	Two-color LED: green for 24 V o.k., red for overload
type of signal at output	DC OK via relay contact, current monitor signal (0 to 2.5 V correspond to 0 to 10 A)
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	0.5 s
voltage increase time of the output voltage	
• typical	20 ms
output current	
• rated value	10 A
• rated range	0 ... 10 A; Output power max. 120 W
supplied active power typical	120 W
constant overload current	
• on short-circuiting during the start-up typical	12 A
• at short-circuit during operation typical	12 A
product feature	
• bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	88 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	16 W
• during no-load operation maximum	3 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.3 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	5 %
setting time	
• maximum	0.2 ms
Protection and monitoring	
design of the overvoltage protection	≤ 60 V according to EN 60950-1
response value current limitation	2 ... 10 A
design of the current limitation	Can be set with potentiometer or analog control voltage signal 0.5 ... 2.5 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic current limiting (2 ... 10 A) in the range 3 ... 12 V or power limiting (120 W) in the range 12 ... 52 V
enduring short circuit current RMS value	
• maximum	12 A
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra low output voltage Vout according to EN 60950-1
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
protection class IP	IP20
Approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• CSA approval	No; -
• cCSAus, Class 1, Division 2	No
• ATEX	No

certificate of suitability	
• IECEx	No
• NEC Class 2	No
• ULhazloc approval	No
• FM registration	No
type of certification CB-certificate	Yes
certificate of suitability	
• EAC approval	Yes
• C-Tick	Yes
• Regulatory Compliance Mark (RCM)	Yes
certificate of suitability shipbuilding approval	No
shipbuilding approval	-
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• DNV GL	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
EMC	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
environmental conditions	
ambient temperature	
• during operation	-25 ... +70 °C; Derating > 60°C: 2%/°K
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
• at input	L1, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm² single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.5 ... 2.5 mm² single-core/finely stranded
• for auxiliary contacts	Alarm signals, control inputs: screw-type terminals for 0.14 ... 1.5 mm² single-core/finely stranded
width of the enclosure	42 mm
height of the enclosure	125 mm
depth of the enclosure	135 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
net weight	0.55 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 200 000 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6EP33430SA000AY0