



SITOP BAT1600/BATT.MODUL/24V/12AH/EX

SITOP BAT1600 EX 24 V DC 12 Ah Pb battery module with maintenance- free closed lead-acid battery for SITOP UPS1600

### Charging current charging voltage

end-of-charge voltage at DC

• at -10 °C recommended	28 V
• at 0 °C recommended	28 V
• at 10 °C recommended	27.8 V
• at 20 °C recommended	27.3 V
• at 30 °C recommended	26.8 V
• at 40 °C recommended	26.6 V
• at 50 °C recommended	26.3 V

### Output

output current rated value	40 A
charging current maximum	3 A
output voltage at DC rated value	24 V

### Safety

design of the overload protection	Valve control
display version for normal operation	Three-color: green = Buffer ready; yellow = Buffer endangered; red = Buffer not possible

### Safety

operating resource protection class	Class III
protection class IP	IP20

### Approvals

certificate of suitability	
• CE marking	Yes
• UL approval	No
• CSA approval	No
• cCSAus, Class 1, Division 2	No
• ATEX	Yes
certificate of suitability	
• IECEx	Yes
certificate of suitability	
• shipbuilding approval	No
shipbuilding approval	available soon
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• DNV GL	No

### environmental conditions

Operating data note	For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
ambient temperature	

<ul style="list-style-type: none"> <li>• during operation</li> <li>• during transport</li> <li>• during storage</li> </ul>	-15 ... +50 °C -20 ... +50 °C -20 ... +40 °C
relative temporary capacity loss at 20 °C in a month typical	3 %
<b>Service life</b>	
service life of energy storage <ul style="list-style-type: none"> <li>• typical</li> <li>• at 20 °C typical</li> <li>• at 30 °C typical</li> <li>• at 40 °C typical</li> <li>• at 50 °C typical</li> </ul>	capacity falls to 80 % of original capacity (according to EUROBAT) 4 a 2 a 1 a 0.5 a
ambient temperature during storage	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.
<b>Mechanics</b>	
type of electrical connection <ul style="list-style-type: none"> <li>• for power supply unit</li> <li>• for control circuit and status message</li> </ul>	screw-type terminals 1 screw terminal each for 0.5 ... 16 mm² for + BAT and - BAT 1 screw terminal each for 0.2 ... 2.5 mm²
product component included	2x Maxi Fuse 50 A/32 V
width of the enclosure	225 mm
height of the enclosure	156 mm
depth of the enclosure	138 mm
installation width	225 mm
mounting height	256 mm
required spacing <ul style="list-style-type: none"> <li>• top</li> <li>• bottom</li> <li>• left</li> <li>• right</li> </ul>	50 mm 50 mm 0 mm 0 mm
fastening method <ul style="list-style-type: none"> <li>• wall mounting</li> <li>• standard rail mounting</li> <li>• S7 rail mounting</li> </ul>	Yes No No
fastening method	Wall mounting
net weight	10.2 kg
number of cells	2
battery capacity	12 A·h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6EP41350GL000AY0