



SITOP RED1200/RED.M./DC24/48V/2X10A

SITOP RED1200 redundancy module Input/output: 24/48 V DC/20 A Suitable for decoupling two SITOP power supplies with max. 10 A output current each

Input	
type of the power supply network	DC voltage
supply voltage	
• at DC	12 ... 48 V
input voltage	
• at DC	10 ... 58 V
Output	
voltage curve at output	Controlled DC voltage
number of outputs	1
output voltage at DC rated value	24 V
formula for output voltage	$V_{in} - \text{approx. } 0.6 \text{ V}$
output voltage	
• at output 1 at DC rated value	24 V
product function output voltage adjustable	No
output current	
• rated value	20 A
product feature	
• bridging of equipment	No
Efficiency	
efficiency in percent	97.5 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	12 W
• during no-load operation maximum	0.1 W
Safety	
galvanic isolation between input and output	No
operating resource protection class	Class III
protection class IP	IP20
Approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• CSA approval	Yes; CSA C22.2 No. 62368-1
• cCSAus, Class 1, Division 2	No
• ATEX	No
certificate of suitability	
• IECEx	No
• NEC Class 2	No
• ULhazloc approval	No
• FM registration	No

certificate of suitability shipbuilding approval	No
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• DNV GL	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
EMC	
standard	
• for emitted interference	EN 61000-6-3
• for interference immunity	EN 61000-6-2
environmental conditions	
ambient temperature	
• during operation	-30 ... +70 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	push-in terminals
• at input	In1, In2: each for 0.2 ... 10 mm ²
• at output	Out1: 0.2 ... 10 mm ²
width of the enclosure	35 mm
height of the enclosure	135 mm
depth of the enclosure	125 mm
required spacing	
• top	45 mm
• bottom	45 mm
• left	0 mm
• right	0 mm
net weight	0.47 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	8 100 000 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6EP43467RB000AX0](#)