



SCALANCE XB004-1G unmanaged Industrial Ethernet Switch for 10/100/1000 Mbit/s; for setting up small star and line topologies; LED diagnostics, IP20, 24 V DC power supply, with 4x 10/100/1000 Mbit/s RJ45 ports electrical and 1 x 1000 Mbit/s SC-port optical (multimode, glass), up to max. 750 m Manual available as a download .

<b>product type designation</b>	<b>SCALANCE XB004-1G</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	4
number of optical ports / maximum	1
<b>interfaces / for communication / integrated</b>	
number of electrical connections <ul style="list-style-type: none"> <li>• for network components or terminal equipment</li> </ul>	4; RJ45
number of 100 Mbit/s SC ports <ul style="list-style-type: none"> <li>• for multimode</li> </ul>	0
number of 1000 Mbit/s SC ports <ul style="list-style-type: none"> <li>• for multimode</li> </ul>	1
<b>interfaces / other</b>	
number of electrical connections <ul style="list-style-type: none"> <li>• for power supply</li> </ul>	1
type of electrical connection <ul style="list-style-type: none"> <li>• for power supply</li> </ul>	3-pole terminal block
<b>supply voltage, current consumption, power loss</b>	
<b>type of voltage / 1 / of the supply voltage</b>	DC
<ul style="list-style-type: none"> <li>• supply voltage / 1 / rated value</li> <li>• power loss [W] / 1 / rated value</li> <li>• supply voltage / 1 / rated value</li> <li>• consumed current / 1 / maximum</li> <li>• type of electrical connection / 1 / for power supply</li> <li>• product component / 1 / fusing at power supply input</li> <li>• fuse protection type / 1 / at input for supply voltage</li> </ul>	24 V 12.5 W 19.2 ... 28.8 V 0.52 A 3-pole terminal block Yes 0.6 A / 60 V
<b>ambient conditions</b>	
ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> </ul>	-10 ... +60 °C -40 ... +80 °C -40 ... +80 °C
relative humidity <ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	Box
width	45 mm
height	100 mm

depth	87 mm
net weight	0.21 kg
fastening method	
• 35 mm top hat DIN rail mounting	Yes
• wall mounting	Yes
• S7-1500 rail mounting	No
<b>product functions / management, configuration, engineering</b>	
product function	
• multiport mirroring	No
• CoS	Yes
PROFINET conformity class	A
product function / switch-managed	No
<b>product functions / redundancy</b>	
product function	
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
<b>standards, specifications, approvals</b>	
standard	
• for FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2
MTBF	124 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0:2009, EN60079-15:2010, II 3 G Ex nA IIC T4 Gc, KEMA 07ATEX0145 X
certificate of suitability	
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
• KC approval	Yes
<b>further information / internet links</b>	
internet link	
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to website: Industrial communication	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAX-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a> . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a> . (V3.4)
last modified:	5/27/2023 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK50041GL101AB2](#)