




SCALANCE XF204IRT, flat, Managed IE IRT switch, 4x 10/100 Mbit/s RJ45 ports, Error signaling contact with set pushbutton, redundant power supply, PROFINET IO device, network management, Redundancy Manager integrated, incl. electron. manual on CD-ROM, C-PLUG optional.

<b>product type designation</b>	<b>SCALANCE XF204IRT</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	4
<b>interfaces / for communication / integrated</b>	
number of electrical connections	
• for network components or terminal equipment	4
<b>interfaces / other</b>	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
<b>supply voltage, current consumption, power loss</b>	
product component / connection for redundant voltage supply	Yes
<b>type of voltage / 1 / of the supply voltage</b>	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	4.8 W
• supply voltage / 1 / rated value	18 ... 32 V
• consumed current / 1 / maximum	0.2 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	0.6 A / 60 V
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +60 °C
• during transport	-40 ... +60 °C
• note	If the IE-Switch XF-200 is installed horizontally, a maximum ambient temperature of +40 °C is permitted
relative humidity	

<ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	Flat
width	75 mm
height	125 mm
depth	73 mm
net weight	0.25 kg
fastening method	
<ul style="list-style-type: none"> <li>• 35 mm top hat DIN rail mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• wall mounting</li> </ul>	No
<ul style="list-style-type: none"> <li>• S7-300 rail mounting</li> </ul>	No
<ul style="list-style-type: none"> <li>• S7-1500 rail mounting</li> </ul>	No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function	
<ul style="list-style-type: none"> <li>• CLI</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• web-based management</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• MIB support</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TRAPs via email</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• configuration with STEP 7</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• port mirroring</li> </ul>	No
<ul style="list-style-type: none"> <li>• multiport mirroring</li> </ul>	No
<ul style="list-style-type: none"> <li>• with IRT / PROFINET IO switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• PROFINET IO diagnosis</li> </ul>	Yes
PROFINET conformity class	C
network load class / according to PROFINET	2
product function / switch-managed	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• Telnet</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTPS</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TFTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• FTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• BOOTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• DCP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• LLDP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v1</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v2</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v3</li> </ul>	Yes
identification & maintenance function	
<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• I&amp;M1 - higher level designation/location designation</li> </ul>	Yes
<b>product functions / diagnostics</b>	
product function	
<ul style="list-style-type: none"> <li>• port diagnostics</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics Packet Size</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics packet type</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• error statistics</li> </ul>	Yes
<b>product functions / DHCP</b>	
product function	
<ul style="list-style-type: none"> <li>• DHCP client</li> </ul>	Yes
<b>product functions / redundancy</b>	
product function	
<ul style="list-style-type: none"> <li>• ring redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with redundancy</li> </ul>	Yes

manager	
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> <li>• media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Media Redundancy Protocol for Planned Duplication (MRPD)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/operation in the PRP-network</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	No
<ul style="list-style-type: none"> <li>• passive listening</li> </ul>	Yes
<b>product functions / security</b>	
protocol / is supported	
<ul style="list-style-type: none"> <li>• SSH</li> </ul>	Yes
<b>product functions / time</b>	
product function	
<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>• for FM</li> </ul>	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4, FM16US0205X
<ul style="list-style-type: none"> <li>• for emitted interference</li> </ul>	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> <li>• for interference immunity</li> </ul>	EN 61000-6-4:2001
MTBF	80.58 a
reference code	
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> </ul>	KF
<ul style="list-style-type: none"> <li>• according to IEC 81346-2:2019</li> </ul>	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X
<ul style="list-style-type: none"> <li>• from CSA and UL</li> </ul>	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4, E240480
certificate of suitability	
<ul style="list-style-type: none"> <li>• CCC / for hazardous zone according to GB standard</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• CCC / for hazardous zone according to GB standard / as marking</li> </ul>	Ex nA IIC T4 Gc
<ul style="list-style-type: none"> <li>• for cULus HazLoc / as File Nr.</li> </ul>	E240480 (NWHP, NWHP7)
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-4:2001
<ul style="list-style-type: none"> <li>• C-Tick</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• KC approval</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• railway application in accordance with EN 50155</li> </ul>	No
<ul style="list-style-type: none"> <li>• railway application in accordance with EN 50124-1</li> </ul>	No
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
<ul style="list-style-type: none"> <li>• American Bureau of Shipping Europe Ltd. (ABS)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• French marine classification society (BV)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Det Norske Veritas (DNV)</li> </ul>	No
<ul style="list-style-type: none"> <li>• Germanische Lloyd (GL)</li> </ul>	No
<ul style="list-style-type: none"> <li>• DNV GL</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Lloyds Register of Shipping (LRS)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Nippon Kaiji Kyokai (NK)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Polski Rejestr Statkow (PRS)</li> </ul>	No
<ul style="list-style-type: none"> <li>• Royal Institution of Naval Architects (RINA)</li> </ul>	Yes
<b>accessories</b>	

product extension / optional / C-PLUG	Yes
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAX-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a>. (V3.4)</p>
last modified:	8/18/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52040BA002BF2](#)