



SCALANCE X204RNA EEC; redundant network access 2x 100 Mbit/s RJ45 ports; 2x 100 Mbit/s combo ports; LED diagnostics; error signaling contact with set pushbutton; simple power supply; network management; including electronic manual on CD-ROM, C-PLUG optional for PRP network

<b>product type designation</b>	<b>SCALANCE X204RNA EEC</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	4
<b>interfaces / for communication / integrated</b>	
number of electrical connections	
• for network components or terminal equipment	2
number of combo ports / with RJ45 interface for optical plug-in transceiver	2
<b>interfaces / other</b>	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	3-pole terminal block
• for power supply	3-pole terminal block
design of the removable storage	
• C-PLUG	Yes
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts	
• at AC / rated value	230 V
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at AC / maximum	0.1 A
• at DC / maximum	0.1 A
<b>supply voltage, current consumption, power loss</b>	
product component / connection for redundant voltage supply	Yes
<b>type of voltage / 1 / of the supply voltage</b>	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	6 W
• supply voltage / 1 / rated value	85 ... 276 V
• consumed current / 1 / maximum	0.25 A
• type of electrical connection / 1 / for power supply	3-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	1.25 A
<b>type of voltage / 2 / of the supply voltage</b>	
• supply voltage / 2 / rated value	85 ... 276 V
<b>ambient conditions</b>	
ambient temperature	

<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> <li>during transport</li> <li>note</li> </ul>	-40 ... +70 °C -40 ... +70 °C -40 ... +70 °C A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
relative humidity <ul style="list-style-type: none"> <li>at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	compact
width	70 mm
height	147 mm
depth	123 mm
net weight	0.78 kg
product feature / conformal coating	Yes
fastening method <ul style="list-style-type: none"> <li>35 mm top hat DIN rail mounting</li> <li>wall mounting</li> <li>S7-300 rail mounting</li> <li>S7-1500 rail mounting</li> </ul>	Yes No No No
<b>product functions / management, configuration, engineering</b>	
product function <ul style="list-style-type: none"> <li>CLI</li> <li>web-based management</li> <li>MIB support</li> <li>TRAPs via email</li> <li>configuration with STEP 7</li> <li>port mirroring</li> <li>multiport mirroring</li> <li>with IRT / PROFINET IO switch</li> <li>PROFINET IO diagnosis</li> </ul>	Yes Yes Yes Yes No No No No No
product function / switch-managed	No
protocol / is supported <ul style="list-style-type: none"> <li>Telnet</li> <li>HTTP</li> <li>HTTPS</li> <li>TFTP</li> <li>FTP</li> <li>BOOTP</li> <li>GMRP</li> <li>DCP</li> <li>LLDP</li> <li>SNMP v1</li> <li>SNMP v2</li> <li>SNMP v3</li> <li>IGMP (snooping/querier)</li> </ul>	No Yes Yes No No No No Yes No Yes Yes Yes Yes No
identification & maintenance function <ul style="list-style-type: none"> <li>I&amp;M0 - device-specific information</li> <li>I&amp;M1 - higher level designation/location designation</li> </ul>	Yes Yes
<b>product functions / diagnostics</b>	
product function <ul style="list-style-type: none"> <li>port diagnostics</li> <li>statistics Packet Size</li> <li>statistics packet type</li> <li>error statistics</li> </ul>	Yes Yes Yes Yes
<b>product functions / redundancy</b>	
product function <ul style="list-style-type: none"> <li>ring redundancy</li> <li>High Speed Redundancy Protocol (HRP)</li> <li>high speed redundancy protocol (HRP) with redundancy</li> </ul>	No No No

manager	
• high speed redundancy protocol (HRP) with standby redundancy	No
protocol / is supported / Media Redundancy Protocol (MRP)	No
product function	
• media redundancy protocol (MRP) with redundancy manager	No
• High-availability Seamless Redundancy (HSR)	No
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	Yes
• High-availability Seamless Redundancy (HSR) and Parallel Redundancy Protocol (PRP) coupling	No
• passive listening	No
<b>product functions / security</b>	
protocol / is supported	
• SSH	Yes
<b>product functions / time</b>	
product function	
• SICLOCK support	No
protocol / is supported	
• NTP	No
• SNTP	Yes
<b>standards, specifications, approvals</b>	
standard	
• for FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4, FM16US0205X
• for safety / from CSA and UL	UL 508 E85972, CSA C22.2 no. 142-M1987
• for emitted interference	EN 61000-6-4:2001 (Class A)
• for interference immunity	EN 61000-6-4:2001
MTBF	67.64 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
standard	
• for EMC	IEC 61850, IEEE 1613
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-4:2001
• C-Tick	Yes
• KC approval	Yes
• railway application in accordance with EN 50155	Yes
• railway application in accordance with EN 50121-4	Yes
• railway application in accordance with EN 50124-1	No
• fire protection in accordance with EN 45545-2	Yes
• IEC 61850-3	Yes
• IEEE 1613	Yes
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	Yes
• DNV GL	Yes
• Korean Register of Shipping (KRS)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	Yes
• Royal Institution of Naval Architects (RINA)	Yes
<b>accessories</b>	
product extension / optional / C-PLUG	Yes

#### further information / internet links

##### internet link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>  
<http://www.siemens.com/simatic-net>  
<https://mall.industry.siemens.com>  
<http://www.siemens.com/industry/infocenter>  
<http://automation.siemens.com/bilddb>  
<http://www.siemens.com/cax>  
<https://support.industry.siemens.com>

#### security information

##### security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

##### last modified:

7/1/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52040BS003LA3](#)