



XF204-2BA IRT managed IE IRT switch, 4 x 10/100 Mbit/s, 2 x Bus adapter interface, error signaling contact, with set pushbutton, redundant 24 V DC power supply, PROFINET IO device, network management, Redundancy Manager integrated, incl. electron. manual on CD-ROM, C-PLUG optional.

product type designation	SCALANCE XF204-2BA IRT
product options	XF-200 base device without mounted BusAdapter
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	4
number of optical ports / maximum	2
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	0
interfaces / other	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	2-pole terminal block
design of the removable storage	
• C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	2.4 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	0.1 A
• type of electrical connection / 1 / for power supply	2-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	2.5 A (cannot be changed by user)
ambient conditions	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	

<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	100 mm
height	117 mm
depth	74 mm
net weight	0.25 kg
fastening method	
<ul style="list-style-type: none"> • 35 mm top hat DIN rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	No
<ul style="list-style-type: none"> • S7-300 rail mounting 	No
<ul style="list-style-type: none"> • S7-1500 rail mounting 	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
<ul style="list-style-type: none"> • CLI 	Yes
<ul style="list-style-type: none"> • web-based management 	Yes
<ul style="list-style-type: none"> • MIB support 	Yes
<ul style="list-style-type: none"> • TRAPs via email 	Yes
<ul style="list-style-type: none"> • configuration with STEP 7 	Yes
<ul style="list-style-type: none"> • port mirroring 	No
<ul style="list-style-type: none"> • multiport mirroring 	No
<ul style="list-style-type: none"> • with IRT / PROFINET IO switch 	Yes
<ul style="list-style-type: none"> • PROFINET IO diagnosis 	Yes
PROFINET conformity class	C
network load class / according to PROFINET	2
product function / switch-managed	Yes
protocol / is supported	
<ul style="list-style-type: none"> • Telnet 	Yes
<ul style="list-style-type: none"> • HTTP 	Yes
<ul style="list-style-type: none"> • HTTPS 	Yes
<ul style="list-style-type: none"> • TFTP 	Yes
<ul style="list-style-type: none"> • FTP 	Yes
<ul style="list-style-type: none"> • BOOTP 	No
<ul style="list-style-type: none"> • DCP 	Yes
<ul style="list-style-type: none"> • LLDP 	Yes
<ul style="list-style-type: none"> • SNMP v1 	Yes
<ul style="list-style-type: none"> • SNMP v2 	Yes
<ul style="list-style-type: none"> • SNMP v3 	Yes
identification & maintenance function	
<ul style="list-style-type: none"> • I&M0 - device-specific information 	Yes
<ul style="list-style-type: none"> • I&M1 - higher level designation/location designation 	Yes
product functions / diagnostics	
product function	
<ul style="list-style-type: none"> • port diagnostics 	Yes
<ul style="list-style-type: none"> • statistics Packet Size 	Yes
<ul style="list-style-type: none"> • statistics packet type 	Yes
<ul style="list-style-type: none"> • error statistics 	Yes
product functions / DHCP	
product function	
<ul style="list-style-type: none"> • DHCP client 	Yes
product functions / redundancy	
product function	
<ul style="list-style-type: none"> • ring redundancy 	Yes
<ul style="list-style-type: none"> • High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy 	Yes

manager	
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Media Redundancy Protocol for Planned Duplication (MRPD) 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • passive listening 	Yes
product functions / security	
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	No
<ul style="list-style-type: none"> • SNTP 	Yes
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4, FM16US0205X
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2, EN 61000-6-4
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	KF
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4, E223122
certificate of suitability	
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard 	Yes
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard / as marking 	Ex nA IIC T4 Gc
standards, specifications, approvals / other	
certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • railway application in accordance with EN 50155 	No
<ul style="list-style-type: none"> • railway application in accordance with EN 50124-1 	No
standards, specifications, approvals / marine classification	
Marine classification association	
<ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
<ul style="list-style-type: none"> • Korean Register of Shipping (KRS) 	Yes
accessories	
product extension / optional / C-PLUG	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAX-Download-Manager 	http://www.siemens.com/cax

security information

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52042AA002BD2](#)