



SCALANCE XB205-3 managed Layer 2 IE switch 5x 10/100 Mbit/s RJ45 ports 3x MM FO ST port 1x console port, diagnostics LED redundant power supply; IEC 62443-4-2 certified; temperature range 0 °C to +60 °C; DIN-rail mounting; default PROFINET.

product type designation	SCALANCE XB205-3
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s
number of ports / maximum	8
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	5
number of optical ports / maximum	3
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	5; RJ45
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	3
interfaces / other	
number of electrical connections	
• for operator console	1
• for management purposes	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for management purposes	RJ45
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	7.2 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	0.3 A
• type of electrical connection / 1 / for power supply	6-pole terminal block
• product component / 1 / fusing at power supply input	Yes
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	Box

width	80 mm
height	117 mm
depth	109 mm
net weight	0.35 kg
material / of the enclosure	Plastic
fastening method	
• 35 mm top hat DIN rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	No
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	1522 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product function	
• is supported / identification link	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
• loopback diagnostics	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
product functions / redundancy	
product function	
• ring redundancy	Yes

<ul style="list-style-type: none"> • High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Media Redundancy Protocol Interconnection (MRP-I) 	Yes
<ul style="list-style-type: none"> • redundancy procedure STP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP+ 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	No
<ul style="list-style-type: none"> • passive listening 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> • ACL - MAC-based 	Yes
<ul style="list-style-type: none"> • ACL - port/MAC-based 	Yes
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
<ul style="list-style-type: none"> • SSL 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
<ul style="list-style-type: none"> • NTP-client 	Yes
<ul style="list-style-type: none"> • SNTP client 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SNTP 	Yes
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4, FM19US0167X
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	KF
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T6, E240480
certificate of suitability	
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard 	Yes
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard / as marking 	Ex nA IIC T4 Gc
<ul style="list-style-type: none"> • for cULus HazLoc / as File Nr. 	E240480 (NWHP, NWHP7)
standards, specifications, approvals / other	
certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes

further information / internet links

internet link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>
<http://www.siemens.com/simatic-net>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK52053BB002AB2