



SCALANCE XC216-4C G manageable Layer 2 IE switch; IEC 62443-4-2 certified; Full gigabit; 12x 10/100/1000 Mbps RJ45 ports; 4x 1000 Mbps combo ports (either 1000 Mbps/ SFPs or 10/100/1000 Mbps RJ45 ports can be used); 1x console port; diagnostics LED; redundant power supply; temperature range -40 °C to +70 °C; assembly: DIN rail/S7 mounting rail/wall; redundancy functions; office features (RSTP, VLAN,...); PROFINET IO device; Ethernet/IP-compliant; C-PLUG slot; IEEE 1588v2 PTP

product type designation	SCALANCE XC216-4C G
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	16
number of optical ports / maximum	4
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	16; RJ45
number of 10/100/1000 Mbit/s RJ45 ports / integrated	16
number of combo ports / with RJ45 interface for optical plug-in transceiver	4; 1000 Mbit/s SFPs
interfaces / for communication / plug-in	
number of electrical connections	
• for SFP	4; 1000 Mbit/s SFP plug-in transceiver or 100 Mbit/s via SCALANCE SFP991-1(LD) A
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	3-pole terminal block, permanently installed
design of the removable storage	
• C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	13.2 W
• consumed current / 1 / at rated supply voltage / maximum	0.55 A
• supply voltage / 1 / rated value	9.6 ... 31.2 V
• type of electrical connection / 1 / for power supply	3-pole terminal block, permanently installed
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	3.15 A / 125 V

ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	140 mm
height	150 mm
depth	125 mm
net weight	1.2 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
• 35 mm top hat DIN rail mounting	Yes
• wall mounting	No
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function / QoS according to DSCP	Yes
product feature	
• Cut Through switching method	No
• Store & Forward switching method	Yes
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• SMTP server	No
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
network load class / according to PROFINET	3
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	10240 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• BOOTP	No
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	

<ul style="list-style-type: none"> • I&M0 - device-specific information 	Yes
<ul style="list-style-type: none"> • I&M1 - higher level designation/location designation 	Yes
product functions / diagnostics	
product function	
<ul style="list-style-type: none"> • port diagnostics 	Yes
<ul style="list-style-type: none"> • statistics Packet Size 	Yes
<ul style="list-style-type: none"> • statistics packet type 	Yes
<ul style="list-style-type: none"> • error statistics 	Yes
<ul style="list-style-type: none"> • SysLog 	Yes
product functions / VLAN	
product function	
<ul style="list-style-type: none"> • VLAN - port based 	Yes
<ul style="list-style-type: none"> • VLAN - protocol-based 	No
<ul style="list-style-type: none"> • VLAN - IP-based 	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
<ul style="list-style-type: none"> • DHCP server 	Yes
<ul style="list-style-type: none"> • DHCP client 	Yes
<ul style="list-style-type: none"> • DHCP Option 82 	Yes
<ul style="list-style-type: none"> • DHCP Option 66 	Yes
<ul style="list-style-type: none"> • DHCP Option 67 	Yes
product functions / redundancy	
product function	
<ul style="list-style-type: none"> • of the PROFINET IO device / is supported / PROFINET system redundancy 	Yes
<ul style="list-style-type: none"> • ring redundancy 	Yes
<ul style="list-style-type: none"> • High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Media Redundancy Protocol Interconnection (MRP-I) 	Yes
<ul style="list-style-type: none"> • of the PROFINET IO device / is supported / H-Sync forwarding 	Yes
<ul style="list-style-type: none"> • redundancy procedure STP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP+ 	Yes
<ul style="list-style-type: none"> • redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • passive listening 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
<ul style="list-style-type: none"> • SSL 	Yes
product functions / time	

product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
standards, specifications, approvals	
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	46 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-13
• for immunity to EMC	EN 61000-6-2, EN 50121-4
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
accessories	
product extension / optional / C-PLUG	Yes
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52164GS002AC2](#)