

SCALANCE XR328-4C WG; managed IE switch; 19" rack; 24 x 10/ 100/1000 Mbit/s electrical ports; 4 x 1000 Mbit/s combo ports electrical or optical; LED diagnostics; reset button; console port; PROFINET device; network management function; redundancy manager; power supply 24 V DC; IEC 62443-4-2 certified;



product type designation	SCALANCE XR328-4C WG
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	28
number of optical ports / maximum	4
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	28; RJ45
number of 10/100/1000 Mbit/s RJ45 ports / integrated	24
number of combo ports / with RJ45 interface for optical plug-in transceiver	4; 1000 Mbit/s SFP plug-in transceiver or 100 Mbit/s via SCALANCE SFP991-1 (LD) A
interfaces / other	
number of electrical connections	
• for operator console	1
• for power supply	1
type of electrical connection	
• for power supply	2 x 2-pin terminal block
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	21.6 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	0.9 A
• type of electrical connection / 1 / for power supply	2 x 2-pole terminal block
• product component / 1 / fusing at power supply input	Yes
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP30
design, dimensions and weights	
design	19" rack
number of modular height units / relating to 19-inch cabinet	1

width	483 mm
height	44 mm
depth	127 mm
net weight	2.8 kg
material / of the enclosure	metal
fastening method	
• 19-inch installation	Yes
• 35 mm top hat DIN rail mounting	No
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	No
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
network load class / according to PROFINET	2
product function / switch-managed	Yes
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	257

number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	No
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	No
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	No
• RSTP big network support	Yes
• LACP	No
product functions / security	
product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	No
standards, specifications, approvals	
standard	
• for FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1, UL 61010-2-201
• for emitted interference	EN 61000-6-4 (Class B)
• for interference immunity	EN 61000-6-2
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	43 a

reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	KF KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • from CSA and UL 	ANSI/ISA 12.12.01, CAN/CSA C22.2 No. 213-M1987
certificate of suitability	
<ul style="list-style-type: none"> • ATEX • IECEx • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking 	Yes; EN 60079-0, EN60079-15, Ex II 3 G Ex nA II T4 KEMA 07 ATEX 0145X Yes; IEC 60079-0, IEC 60079-15, IECEx DEK 14.0025X, Ex nA IIC T4 Gc Yes Ex nA IIC T4 Gc
standards, specifications, approvals / other	
certificate of suitability	
<ul style="list-style-type: none"> • C-Tick • KC approval • railway application in accordance with EN 50155 	Yes Yes No
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com. (V3.4)</p>

last modified:

5/27/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK53284SS002AR3](#)