

product type designation



W778-1 M12 EEC (USA)

IWLAN access point, SCALANCE W778-1 M12 EEC, 1 radio, 2 N-CON antenna port, iFeatures support via Key-Plug, IEEE 802.11a/b/g/h/n, 2.4/5 GHz, gross data rate 300 Mbps, 2x M12 max. 100 Mbps, PoE integrated 2-port switch, redundant 24 V DC, M12 A-coded IP65, -40...+75 °C, plug slot WPA2/802.11i/e, conformal coating EN 50155, EN45545, observe national approvals! CERT ID: MSN65-W1-M12-E2 Scope of delivery: Manuals on CD-ROM, German/English; M12 sealing caps, for operation in the USA

transfer rate

transfer rate	
• with WLAN / maximum	300 Mbit/s
• for Industrial Ethernet	10, 100 Mbit/s
transfer rate / for Industrial Ethernet	
• minimum	10 Mbit/s
• maximum	100 Mbit/s

interfaces

number of electrical connections	
• for network components or terminal equipment	2
• for power supply	1
• for redundant voltage supply	1
type of electrical connection	
• for network components or terminal equipment	M12 interface (4-pole, D-coded), PoE
• for power supply	M12 interface (4-pole, A-coded)
design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes

memory

design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes

interfaces / wireless

number of radio cards / permanently installed	1
transmission mode / for multiple input multiple output (MIMO)	2x2
number of spatial streams	2
number of electrical connections / for external antenna(s)	2
type of electrical connection / for external antenna(s)	N-Connect (socket)
product feature / external antenna can be mounted directly on device	Yes

supply voltage, current consumption, power loss

type of voltage / of the supply voltage	DC
supply voltage	
• from Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af	48 V
consumed current	
• at DC / at 24 V / typical	0.25 A
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.125 A
power loss [W]	

<ul style="list-style-type: none"> • at DC / at 24 V / typical • with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical 	6 W 6 W
supply voltage / 1	
<ul style="list-style-type: none"> • from M12 Power Connector (A-coded) for redundant power supply 	16.8 V
supply voltage / 2	
<ul style="list-style-type: none"> • from M12 Power Connector (A-coded) for redundant power supply 	31.2 V
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport 	-40 ... +75 °C -40 ... +85 °C -40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W778-1 M12 or W738-1 M12 product must be installed in an housing with at least IP54 degree of protection according to EN 60529 within the scope of EN 50021.
protection class IP	IP65
design, dimensions and weights	
width	140 mm
height	160 mm
depth	45 mm
width / of the enclosure / without antenna	140 mm
height / of the enclosure / without antenna	149 mm
depth / of the enclosure / without antenna	45 mm
net weight	0.95 kg
product feature / conformal coating	Yes
fastening method	35 mm DIN rail mounting only per accessories
<ul style="list-style-type: none"> • S7-300 rail mounting • S7-1500 rail mounting • 35 mm top hat DIN rail mounting • wall mounting 	No No Yes Yes
radio frequencies	
operating frequency	
<ul style="list-style-type: none"> • for WLAN in 2.4 GHz frequency band • for WLAN in 5 GHz frequency band 	2.41 ... 2.48 GHz; depending on the country approvals 4.9 ... 5.8 GHz; depending on the country approvals
product features, product functions, product components / general	
product function / Access Point Mode	Yes
product function / client Mode	Yes
number of SSIDs	4
product function	
<ul style="list-style-type: none"> • iPCF Access Point • iPCF client • iPCF-MC Access Point • iPCF-MC client 	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures' No Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	1
product function / iREF	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iREF-capable radio modules	1
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' only
product functions / management, configuration, engineering	
number of manageable IP addresses / in client	8
product function	
<ul style="list-style-type: none"> • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • configuration with STEP 7 in the TIA Portal 	Yes Yes Yes Yes Yes Yes

<ul style="list-style-type: none"> • operation with IWLAN controller • operation with Enterasys WLAN controller • forced roaming on IP down with IWLAN • forced roaming on link down with IWLAN • WDS 	No No Yes Yes Yes
protocol / is supported <ul style="list-style-type: none"> • Address Resolution Protocol (ARP) • ICMP • Telnet • HTTP • HTTPS • TFTP • DCP • LLDP 	Yes Yes Yes Yes Yes Yes Yes Yes
identification & maintenance function <ul style="list-style-type: none"> • I&M0 - device-specific information • I&M1 - higher level designation/location designation 	Yes Yes
product functions / diagnostics	
product function <ul style="list-style-type: none"> • PROFINET IO diagnosis • link check • connection monitoring IP-Alive • localization via Aeroscout • SysLog 	Yes No No Yes Yes
protocol / is supported <ul style="list-style-type: none"> • SNMP v1 • SNMP v2 • SNMP v3 	Yes Yes Yes
product functions / VLAN	
product function <ul style="list-style-type: none"> • function VLAN with IWLAN 	Yes
product functions / DHCP	
product function <ul style="list-style-type: none"> • DHCP client • DHCP server • DHCP Option 82 	Yes Yes Yes
product functions / redundancy	
protocol / is supported <ul style="list-style-type: none"> • STP/RSTP • MSTP • RSTP 	Yes Yes Yes
product functions / security	
product function <ul style="list-style-type: none"> • ACL - MAC-based • management security, ACL-IP based • IEEE 802.1x (radius) • NAT/NAPT • access protection according to IEEE802.11i • WPA/WPA2 • TKIP/AES 	Yes Yes Yes Yes Yes Yes Yes
protocol / is supported <ul style="list-style-type: none"> • SSH • RADIUS 	Yes Yes
product functions / time	
protocol / is supported <ul style="list-style-type: none"> • NTP • SNTP • SIMATIC time synchronization (SIMATIC Time) 	Yes Yes Yes
standards, specifications, approvals	
standard	

<ul style="list-style-type: none"> • for FM 	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 61010-2-201 E85972, CSA C22.2 no. 60950-1
certificate of suitability <ul style="list-style-type: none"> • EC Declaration of Conformity • CE marking • C-Tick • E1 approval • railway application in accordance with EN 50155 • railway application in accordance with EN 50121-4 • fire protection in accordance with EN 45545-2 • NEMA TS2 • IEC 61375 • IEC 61850-3 • NEMA4X • Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af • Power-over-Ethernet according to IEEE802.3at for type 2 	Yes Yes Yes Yes Yes Yes Yes No No No No Yes Yes
standard for wireless communication <ul style="list-style-type: none"> • IEEE 802.11a • IEEE 802.11b • IEEE 802.11e • IEEE 802.11g • IEEE 802.11h • IEEE 802.11i • IEEE 802.11n 	Yes Yes Yes Yes Yes Yes Yes
wireless approval	You will find the current list of countries at: www.siemens.de/funkzulassungen
standards, specifications, approvals / marine classification	
Marine classification association <ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Korean Register of Shipping (KRS) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) • Royal Institution of Naval Architects (RINA) 	Yes Yes Yes Yes Yes Yes Yes Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone <ul style="list-style-type: none"> • from CSA and UL 	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480
certificate of suitability / CCC / for hazardous zone according to GB standard <ul style="list-style-type: none"> • as marking 	Yes Ex nA IIC T4 Gc
further information / internet links	
internet link <ul style="list-style-type: none"> • to website: TIA Selection Tool • to web page: selection aid TIA Selection Tool • to the website: IWLAN • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/tia-selection-tool http://www.siemens.com/iwlan https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial

security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

7/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57781GY000TB0