

product type designation



SFP992-1

SCALANCE X accessory; Plug-in transceiver SFP992-1; 1x 1000 Mbit/s LC port, optical; multimode optical up to max. 750 m.

interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of optical interfaces / for network components or terminal equipment / maximum	1
number of 1000 Mbit/s LC ports / for multimode / integrated	1
design of the optical interface / for network components or terminal equipment	LC
wavelength / of the optical interface	850 nm; Multi-mode
connectable optical power relative to 1 mW	
• of the transmitter output / minimum	-9.5 dB
• of the transmitter output / maximum	-2.5 dB
• of the receiver input / maximum	-3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-17 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0.35 ... 0.75 km
ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
• note	A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	SFP Module
width	14 mm
height	9 mm
depth	57 mm
net weight	0.01 kg
fastening method	latched
standards, specifications, approvals	
standard	
• for FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X

• for safety / from CSA and UL • for emitted interference • for interference immunity	UL 60950-1, CSA C22.2 No. 60950-1-03 EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes No Yes Ex nA IIC T4 Gc
Marine classification association • French marine classification society (BV)	Yes
MTBF	670 a
further information / internet links	
internet link • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK59921AL008AA0