

product type designation

MM992-4SFP

SCALANCE X accessory; Media module MM992-4SFP; 4x 100/1000 Mbit/s for SFP plug-in transceiver.



interfaces

number of electrical/optical connections / for network components or terminal equipment / maximum	4
number of electrical connections	
• for SFP / plug-in	4

ambient conditions

ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20

design, dimensions and weights

design	Media module
width	120.3 mm
height	22.3 mm
depth	275.5 mm
net weight	0.3 kg
fastening method	latched
• installation in media module slot	Yes

standards, specifications, approvals

standard	
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-3
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
• CE marking	Yes
• C-Tick	Yes
• KC approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
• E1 approval	No
Marine classification association	
• French marine classification society (BV)	Yes

further information / internet links

internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK59924AS008AA0