

Data sheet for Braking Module

Article No. : 6SL3201-2AD20-8VA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
Rated power P _{DB}	2.75 kW
Rated power, max.	5.50 kW
Activation threshold 230V / 400V	388 V (782 V)
Switch to select 230V / 400V	

General technical specifications	
DC link voltage	DC 250 ... 800 V

Current carrying capacity	
DC link busbar 230V / 400V	8.0 A / 5.2 A

Mechanical data	
Net weight	0.7 kg (1.54 lb)
Dimensions	
Width	90 mm (3.54 in)
Height	150 mm (5.91 in)
Depth	88 mm (3.46 in)

Connections	
-------------	--

PE connection	
Version on housing	M4 screw

BrakeResistor	
Connection cross-section, max.	4.0 mm² (12 AWG)
Cable length to braking resistor, max.	10.0 m (32.81 ft)

Standards	
Compliance with standards	CE, cULus

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6SL32012AD208VA0](#)