

## Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE25-5UV0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :



Figure similar

### Rated data

#### Input

Number of phases	3 AC
Line voltage	380 ... 480 V -15 % +10 %
Line frequency	47 ... 63 Hz

#### Output

Number of phases	3 AC	
<b>Rated voltage</b>	<b>400V IEC</b>	<b>480V NEC <sup>1)</sup></b>
Rated power (LO)	5.50 kW	7.50 hp
Rated power (HO)	5.50 kW	7.50 hp
Rated current (LO)	12.50 A	11.00 A
Rated current (HO)	12.50 A	11.00 A
Rated current (IN)	12.50 A	
Pulse frequency	4.00 kHz	
Output frequency	0 ... 550 Hz	

#### Overload capability

Low Overload (LO)
110 % rated output current for 60 s, cycle time 300 s
High Overload (HO)
150 % rated output current for 60 s, cycle time 300 s

### General tech. specifications

Power factor $\lambda$	0.72
Offset factor $\cos \varphi$	0.95
Efficiency $\eta$	0.98
Filter class (integrated)	Unfiltered

### Communication

Communication	USS, Modbus RTU
---------------	-----------------

### Inputs / outputs

#### Standard digital inputs

Number	4
--------	---

#### Digital outputs

Number as relay changeover contact	1
Number as transistor	1

#### Analog inputs

Number	2 (Can be used as additional digital input)
--------	---

#### Analog outputs

Number	1
--------	---

### Ambient conditions

Cooling	External fan
Installation altitude	1,000 m (3,280.84 ft)
<b>Ambient temperature</b>	
Operation <sup>2)</sup>	-10 ... 60 °C (14 ... 140 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

#### Relative humidity

Max. operation	95 %
----------------	------

### Connections

#### Max. motor cable length

Shielded	25 m (82.02 ft)
Unshielded	50 m (164.04 ft)

### Mechanical data

Mounting position	Through-hole mounting / wall mounting / side-by-side mounting
Degree of protection	IP20 / UL open type
Frame size	FSC
Net weight	2.40 kg (5.29 lb)

#### Dimensions

Width	184.0 mm (7.24 in)
Height	182.0 mm (7.17 in)
Depth	169.0 mm (6.65 in)


### Standards

Compliance with standards	CE, cULus, C-Tick (RCM), KC
CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE25-5UV0

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	35.2 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 440V-480V

<sup>2)</sup> Please observe derating at temperatures of 40 °C or above

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6SL32105BE255UV0