



Circuit breaker 3VA6 UL Frame 600 breaking capacity class C 100kA @ 480 V 3-pole, Line protection ETU856, LSI, In=400A overload protection, 100% rated Ir=160A ...400A Short-circuit protection Isd=0.6..10x In, li=1.5..12x In N conductor protection optionally with external CT; up to 160% Ground-fault alarm message via EFB300 or COM nut keeper kit on both sides

| Model  |   |
|--|---|
| product brand name   | SENTRON                                 |
| product designation  | Molded-case circuit breaker             |
| product designation / according to UL file   | CLAE                                    |
| design of the product  | System protection                       |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                                     |
| design of the overcurrent release  | ETU856                                  |
| protection function of the overcurrent release   | LSI-G-alarm only                        |
| number of poles  | 3                                       |
| General technical data   |   |
| insulation voltage / rated value   | 800 V                                   |
| operating voltage / at AC / rated value  | 690 V                                   |
| power loss [W] / maximum   | 70 W                                    |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole                                | 23.33 W                                 |
| mechanical service life (operating cycles) / typical   | 20 000                                  |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V   | 4 000                                   |
| electrical endurance (operating cycles) / at AC-1 / at 690 V   | 3 500                                   |
| electrical endurance (operating cycles) / at 480 V   | 4 000                                   |
| electrical endurance (operating cycles) / at 600 V   | 3 500                                   |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof                      | Yes                                     |
| ground-fault monitoring version  | Summation current formation L-conductor |
| product function   |   |
| • communication function   | Yes                                     |
| • other measurement function   | Yes                                     |
| Net Weight   | 5.596 kg                                |
| Current  |   |
| marking / according to UL 489 / 100%-rated breaker   | Yes                                     |
| operational current  |   |
| • at 40 °C   | 400 A                                   |
| • at 45 °C   | 400 A                                   |
| • at 50 °C   | 400 A                                   |
| • at 55 °C   | 400 A                                   |
| • at 60 °C   | 400 A                                   |
| • at 65 °C   | 400 A                                   |
| • at 70 °C   | 400 A                                   |
| Switching capacity according to IEC 60947  |   |
| switching capacity class of the circuit breaker  | C                                       |
| maximum short-circuit current breaking capacity (Icu)  |   |

|   |                             |
|---|-----------------------------|
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>  | 150 kA<br>110 kA<br>6 kA    |
| operating short-circuit current breaking capacity (Ics) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                                      | 150 kA<br>110 kA<br>6 kA    |
| short-circuit current making capacity (Icm) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>  | 330 kA<br>242 kA<br>9 kA    |
| <b>Switching capacity according to UL 489</b>   |                             |
| current breaking capacity <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 480 V</li> <li>• at 600 V</li> </ul>  | 200 kA<br>100 kA<br>35 kA   |
| <b>Adjustable parameters</b>  |                             |
| adjustable response value setting current (I <sub>r</sub> ) / of the L-trip / with I <sub>2</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul> | 160 A<br>400 A              |
| adjustable response value delay time (t <sub>r</sub> ) / for L-tripping / with I <sub>2</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>     | 0.5 s<br>25 s               |
| adjustable response value setting current (I <sub>sd</sub> ) / of S-trip / with I <sub>0</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>    | 240 A<br>4 000 A            |
| adjustable response value delay time (t <sub>sd</sub> ) / for S-tripping / with I <sub>0</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>    | 0.05 s<br>0.5 s             |
| adjustable response value delay time (t <sub>sd</sub> ) / for S-tripping / with I <sub>2</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> </ul>                       | 0.05 s                      |
| adjustable current response value current / for G-tripping / with standard characteristic <ul style="list-style-type: none"> <li>• initial value</li> <li>• full-scale value</li> </ul>           | 80 A<br>400 A               |
| adjustable response value delay time (t <sub>g</sub> ) / for G-tripping / with I <sub>0</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>     | 0.05 s<br>0.8 s             |
| adjustable response value delay time (t <sub>g</sub> ) / for G-tripping / with I <sub>2</sub> t characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>     | 0.05 s<br>0.8 s             |
| adjustable setting current (I <sub>ln</sub> ) / for N-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>   | 0.2 A<br>1.6 A              |
| adjustable delay time / of S-trip / with I <sub>2</sub> t characteristic  | 0.5 s                       |
| adjustable current response value current / of instantaneous short-circuit trip unit <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                               | 600 A<br>4 800 A            |
| design of the N-conductor protection  | adjustable OFF; 20% to 160% |
| product function / grounding protection   | Yes                         |
| total break time / for G-tripping / with standard characteristic <ul style="list-style-type: none"> <li>• initial value</li> <li>• full-scale value</li> </ul>                                    | 0.05 s<br>0.8 s             |
| <b>Mechanical Design</b>  |                             |
| product component   |                             |

|   |                             |
|---|-----------------------------|
| • undervoltage release  | No                          |
| • voltage trigger   | No                          |
| • trip indicator  | No                          |
| height [in]   | 9.76 in                     |
| height  | 248 mm                      |
| width [in]  | 5.43 in                     |
| width   | 138 mm                      |
| depth [in]  | 4.33 in                     |
| depth   | 110 mm                      |
| <b>Connections</b>  |                             |
| arrangement of electrical connectors / for main current circuit                           | Front connection            |
| type of electrical connection / for main current circuit                                  | nut keeper kit on both ends |
| type of connectable conductor cross-sections / for flat-bar terminal connection / minimum | 20 x 1 mm                   |
| type of connectable conductor cross-sections / for flat-bar terminal connection / maximum | 35 x 10 mm                  |
| <b>Auxiliary circuit</b>  |                             |
| number of CO contacts / for auxiliary contacts  | 0                           |
| <b>Accessories</b>  |                             |
| product extension / optional / motor drive  | Yes                         |
| <b>Environmental conditions</b>   |                             |
| protection class IP / on the front  | IP40                        |
| ambient temperature   |                             |
| • during operation / minimum  | -25 °C                      |
| • during operation / maximum  | 70 °C                       |
| • during storage / minimum  | -40 °C                      |
| • during storage / maximum  | 80 °C                       |
| <b>Certificates</b>   |                             |
| reference code / according to IEC 81346-2   | Q                           |
| certificate of suitability / as approval for NAVAL (no combat vessels) / supplement SB    | Yes                         |
| <b>General Product Approval</b>   |                             |
| <b>Declaration of Conformity</b>  |                             |

[Confirmation](#)



[Miscellaneous](#)



|                           |                   |       |                |
|---------------------------|-------------------|-------|----------------|
| Declaration of Conformity | Marine / Shipping | other | Dangerous Good |
|---------------------------|-------------------|-------|----------------|



[Confirmation](#)

[Miscellaneous](#)

[Transport Information](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA6440-7KT32-2AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA6440-7KT32-2AA0>



Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA6440-7KT32-2AA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA6440-7KT32-2AA0)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications





last modified:

8/14/2023



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA64407KT322AA0](#)