



SITOP PSU100L/1AC/24VDC/2.5A

SITOP PSU100L 24 V/2.5 A Stabilized power supply input: 120/230 V AC, output: DC 24 V/2,5 A

Input	
type of the power supply network	1-phase AC
supply voltage at AC	
• initial value	Set by means of selector switch on the device
supply voltage	
• 1 at AC rated value	120 V
• 2 at AC rated value	230 V
input voltage	
• 1 at AC	93 ... 132 V
• 2 at AC	187 ... 264 V
design of input wide range input	No
overvoltage overload capability	$2.3 \times V_{in}$ rated, 1.3 ms
operating condition of the mains buffering	at $V_{in} = 93/187$ V
buffering time for rated value of the output current in the event of power failure minimum	20 ms
operating condition of the mains buffering	at $V_{in} = 93/187$ V
line frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	1.1 A
• at rated input voltage 230 V	0.65 A
current limitation of inrush current at 25 °C maximum	27 A
duration of inrush current limiting at 25 °C	
• typical	3 ms
I ² t value maximum	0.3 A ² ·s
fuse protection type	T 2 A/250 V (not accessible)
• in the feeder	Recommended miniature circuit breaker: from 3 A characteristic C
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.5 %
residual ripple	
• maximum	150 mV

• typical	10 mV
voltage peak	
• maximum	240 mV
• typical	50 mV
adjustable output voltage	22.8 ... 26.4 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer
display version for normal operation	Green LED for 24 V OK
behavior of the output voltage when switching on	Overshoot of Vout approx. 4 %
response delay maximum	1.5 s
voltage increase time of the output voltage	
• typical	150 ms
output current	
• rated value	2.5 A
• rated range	0 ... 2.5 A; +45 ... +60 °C: Derating 2%/K
supplied active power typical	60 W
product feature	
• bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	85 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	9 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.3 %
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
• load step 10 to 90% typical	0.5 ms
• load step 90 to 10% typical	0.7 ms
Protection and monitoring	
design of the overvoltage protection	< 33 V
• typical	2.6 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Constant current characteristic
enduring short circuit current RMS value	
• typical	4 A
display version for overload and short circuit	-
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
• typical	0.4 mA
protection class IP	IP20
Approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• CSA approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• cCSAus, Class 1, Division 2	No
• ATEX	No
certificate of suitability	
• IECEx	No
• NEC Class 2	No
• ULhazloc approval	No
• FM registration	No
type of certification CB-certificate	Yes

certificate of suitability	
• EAC approval	Yes
certificate of suitability shipbuilding approval	No
shipbuilding approval	-
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• DNV GL	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
EMC	
standard	
• for emitted interference	EN 55022 Class A
• for mains harmonics limitation	not applicable
• for interference immunity	EN 61000-6-2
environmental conditions	
ambient temperature	
• during operation	0 ... 60 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
• at input	L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.5 ... 2.5 mm ²
• for auxiliary contacts	-
width of the enclosure	32.5 mm
height of the enclosure	125 mm
depth of the enclosure	120 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
net weight	0.3 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	3 153 082 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6EP13321LB00