



SITOP MODULAR/3AC/24VDC/20A

SITOP modular 20 A Stabilized power supply input: 400-500 V 3 AC output: 24 V DC/20 A \*Ex approval no longer available\*

Input	
type of the power supply network	3-phase AC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	320 V; Starting from $V_{in} > 340$ V
• full-scale value	550 V
design of input wide range input	Yes
overvoltage overload capability	$2.3 \times V_{in}$ rated, 1.3 ms
operating condition of the mains buffering	at $V_{in} = 400$ V
buffering time for rated value of the output current in the event of power failure minimum	6 ms
operating condition of the mains buffering	at $V_{in} = 400$ V
line frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 400 V	1.1 A
• at rated input voltage 500 V	0.9 A
current limitation of inrush current at 25 °C maximum	35 A
I <sup>2</sup> t value maximum	0.7 A <sup>2</sup> ·s
fuse protection type	none
• in the feeder	Required: 3-pole connected miniature circuit breaker 6 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.2 %
residual ripple	
• maximum	100 mV
voltage peak	
• maximum	200 mV
adjustable output voltage	24 ... 28.8 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer; max. 480 W

display version for normal operation	Green LED for 24 V OK
type of signal at output	via signaling module (6EP1961-3BA10)
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	2.5 s
voltage increase time of the output voltage <ul style="list-style-type: none"> <li>• maximum</li> </ul>	500 ms
output current <ul style="list-style-type: none"> <li>• rated value</li> <li>• rated range</li> </ul>	20 A 0 ... 20 A; +60 ... +70 °C: Derating 2%/K
supplied active power typical	480 W
short-term overload current <ul style="list-style-type: none"> <li>• at short-circuit during operation typical</li> </ul>	60 A
duration of overloading capability for excess current <ul style="list-style-type: none"> <li>• at short-circuit during operation</li> </ul>	25 ms
constant overload current <ul style="list-style-type: none"> <li>• on short-circuiting during the start-up typical</li> </ul>	23 A
product feature <ul style="list-style-type: none"> <li>• bridging of equipment</li> </ul>	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
<b>Efficiency</b>	
efficiency in percent	90 %
power loss [W] <ul style="list-style-type: none"> <li>• at rated output voltage for rated value of the output current typical</li> </ul>	53 W
<b>Closed-loop control</b>	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	2 %
setting time <ul style="list-style-type: none"> <li>• load step 50 to 100% typical</li> <li>• load step 100 to 50% typical</li> </ul>	4 ms 4 ms
setting time <ul style="list-style-type: none"> <li>• maximum</li> </ul>	10 ms
<b>Protection and monitoring</b>	
design of the overvoltage protection <ul style="list-style-type: none"> <li>• typical</li> </ul>	< 35 V 23 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 23 A or latching shutdown
enduring short circuit current RMS value <ul style="list-style-type: none"> <li>• typical</li> </ul>	23 A
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
<b>Safety</b>	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178
operating resource protection class	Class I
leakage current <ul style="list-style-type: none"> <li>• maximum</li> </ul>	3.5 mA
protection class IP	IP20
<b>Approvals</b>	
certificate of suitability <ul style="list-style-type: none"> <li>• CE marking</li> <li>• UL approval</li> <li>• CSA approval</li> <li>• cCSAus, Class 1, Division 2</li> <li>• ATEX</li> </ul>	Yes Yes; UL-Listed (UL 508), File E197259; CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1) Yes; UL-Listed (UL 508), File E197259, CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1) No No
certificate of suitability <ul style="list-style-type: none"> <li>• IECEx</li> <li>• NEC Class 2</li> </ul>	No No

• ULHazloc approval	No
• FM registration	No
type of certification CB-certificate	No
certificate of suitability	
• EAC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS, GL
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	No
• DNV GL	Yes
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
<b>EMC</b>	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
<b>environmental conditions</b>	
ambient temperature	
• during operation	0 ... 70 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
<b>Mechanics</b>	
type of electrical connection	screw-type terminals
• at input	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm² single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.33 ... 4 mm²
• for auxiliary contacts	-
width of the enclosure	160 mm
height of the enclosure	125 mm
depth of the enclosure	125 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
net weight	2 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Buffer module, signaling module
MTBF at 40 °C	711 213 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6EP14363BA00