



SITOP PSU3400/DC/DC/24V/12V/15A

SITOP PSU3400 12 V/15 A Stabilized power supply Input: 24 V DC (14...32 V)
Output: 12 V DC/15 A

Input	
type of the power supply network	DC voltage
supply voltage at AC	
• initial value	Startup as of 18 V, derating necessary for 14 ... 18 V DC
supply voltage	
• at DC	24 ... 24 V
input voltage	
• at DC	14 ... 32 V
design of input wide range input	No
overvoltage overload capability	-
operating condition of the mains buffering	at $V_{in} = 24 \text{ V}$
buffering time for rated value of the output current in the event of power failure minimum	5 ms
operating condition of the mains buffering	at $V_{in} = 24 \text{ V}$
input current	
• at rated input voltage 24 V	8.4 A
current limitation of inrush current at 25 °C maximum	15 A
I^2t value maximum	0.6 A ² s
fuse protection type	25 A (not accessible), breaking capacity 300 A
• in the feeder	Recommended miniature circuit breaker: 16 A characteristic B or C
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	12 V
output voltage	
• at output 1 at DC rated value	12 V
relative overall tolerance of the voltage	2 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.2 %
• on slow fluctuation of ohm loading	1 %
residual ripple	
• maximum	150 mV
• typical	30 mV
voltage peak	
• maximum	250 mV
• typical	50 mV
adjustable output voltage	12 ... 15.5 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer
display version for normal operation	Green LED for 12 V OK
type of signal at output	Relay contact (NO contact, contact rating 30 V AC/0.5 A; 60 V DC/0.3 A; 30 V DC/1 A) for 12 V O.K.

behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	0.5 s
voltage increase time of the output voltage <ul style="list-style-type: none"> • typical • maximum 	5 ms 10 ms
output current <ul style="list-style-type: none"> • rated value • rated range 	15 A 0 ... 15 A; +60 ... +70 °C: Derating 2%/K
supplied active power typical	200 W
product feature <ul style="list-style-type: none"> • bridging of equipment 	Yes
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	91 %
power loss [W] <ul style="list-style-type: none"> • at rated output voltage for rated value of the output current typical • during no-load operation maximum 	21 W 0.5 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.3 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	4 %
setting time <ul style="list-style-type: none"> • load step 50 to 100% typical • load step 100 to 50% typical 	2 ms 2 ms
Protection and monitoring	
design of the overvoltage protection <ul style="list-style-type: none"> • typical 	Ua < 22 V 16 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
display version for overload and short circuit	LED yellow for "overload"
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra low output voltage Vout according to EN 60950-1
operating resource protection class	Class III
protection class IP	IP20
Approvals	
certificate of suitability <ul style="list-style-type: none"> • CE marking • UL approval • CSA approval • cCSAus, Class 1, Division 2 • ATEX 	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 No No
certificate of suitability <ul style="list-style-type: none"> • IECEx • NEC Class 2 • ULhazloc approval • FM registration 	No No No No
type of certification CB-certificate	Yes
certificate of suitability <ul style="list-style-type: none"> • EAC approval • Regulatory Compliance Mark (RCM) 	Yes Yes
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS, DNV GL
Marine classification association <ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) 	Yes No Yes No No

EMC	
standard	
• for emitted interference	EN 61000-6-3
• for mains harmonics limitation	not applicable
• for interference immunity	EN 61000-6-2
environmental conditions	
ambient temperature	
• during operation	-25 ... +70 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
• at input	L, N, FE: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.5 ... 2.5 mm ²
• for auxiliary contacts	Alarm signals: 2 screw terminals for 0.5 ... 2.5 mm ²
• for signaling contact	2 screw terminals for 0.5 ... 2.5 mm ²
width of the enclosure	42 mm
height of the enclosure	125 mm
depth of the enclosure	120 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
net weight	0.6 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Buffer module
MTBF at 40 °C	1 411 273 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6EP31240TA000AY0](#)