



SITOP PSU8200/3AC/24VDC/40A

SITOP PSU8200 24 V/40 A stabilized power supply input: 400-500 V 3 AC output: 24 V DC/40 A *Ex approval no longer available*

Input	
type of the power supply network	3-phase AC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	320 V
• full-scale value	575 V
design of input wide range input	Yes
operating condition of the mains buffering	at $V_{in} = 400 \text{ V}$
buffering time for rated value of the output current in the event of power failure minimum	10 ms
operating condition of the mains buffering	at $V_{in} = 400 \text{ V}$
line frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
line frequency	45 ... 65 Hz
input current	
• at rated input voltage 400 V	2.1 A
• at rated input voltage 500 V	1.7 A
current limitation of inrush current at 25 °C maximum	13 A
I ² t value maximum	2.24 A ² ·s
fuse protection type	none
• in the feeder	Required: 3-pole connected miniature circuit breaker 10 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.2 %
residual ripple	
• maximum	100 mV
voltage peak	
• maximum	240 mV
adjustable output voltage	24 ... 28 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer; max. 960 W
display version for normal operation	Green LED for 24 V OK

type of signal at output	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
behavior of the output voltage when switching on	minimal overshooting (< 2 %)
response delay maximum	0.1 s
voltage increase time of the output voltage <ul style="list-style-type: none"> • maximum 	100 ms
output current <ul style="list-style-type: none"> • rated value • rated range 	40 A 0 ... 40 A; +60 ... +70 °C: Derating 4%/K
supplied active power typical	960 W
short-term overload current <ul style="list-style-type: none"> • at short-circuit during operation typical 	120 A
duration of overloading capability for excess current <ul style="list-style-type: none"> • at short-circuit during operation 	25 ms
constant overload current <ul style="list-style-type: none"> • on short-circuiting during the start-up typical 	44 A
product feature <ul style="list-style-type: none"> • bridging of equipment 	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	94 %
power loss [W] <ul style="list-style-type: none"> • at rated output voltage for rated value of the output current typical • during no-load operation maximum 	66 W 4 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	3 %
setting time <ul style="list-style-type: none"> • maximum 	10 ms
Protection and monitoring	
design of the overvoltage protection <ul style="list-style-type: none"> • typical 	< 31.8 V 44 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 44 A or latching shutdown
enduring short circuit current RMS value <ul style="list-style-type: none"> • typical 	50 A
overcurrent overload capability in normal operation	overload capability 150 % I _{out} rated up to 5 s/min
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
operating resource protection class	Class I
leakage current <ul style="list-style-type: none"> • maximum • typical 	1 mA 0.6 mA
protection class IP	IP20
Approvals	
certificate of suitability <ul style="list-style-type: none"> • CE marking • UL approval • CSA approval • cCSAus, Class 1, Division 2 • ATEX 	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1) Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1) No No
certificate of suitability <ul style="list-style-type: none"> • IECEx • NEC Class 2 • ULhazloc approval 	No No No

• FM registration	No
type of certification CB-certificate	Yes
certificate of suitability	
• EAC approval	Yes
• C-Tick	Yes
• Regulatory Compliance Mark (RCM)	Yes
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS, DNV GL
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	No
• DNV GL	Yes
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
EMC	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
environmental conditions	
ambient temperature	
• during operation	-25 ... +70 °C; With natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
• at input	L1, L2, L3, PE: 1 screw terminal each for 0.5 ... 4 mm ² single-core/finely stranded
• at output	+: 2 screw terminals each for 0.5 ... 16 mm ² ; -: 3 screw terminals each for 0.5 ... 16 mm ²
• for auxiliary contacts	13, 14 (alarm signal), 15, 16 (Remote): 1 screw terminal each for 0.05 ... 2.5 mm ²
width of the enclosure	135 mm
height of the enclosure	145 mm
depth of the enclosure	150 mm
required spacing	
• top	40 mm
• bottom	40 mm
• left	0 mm
• right	0 mm
net weight	3.3 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x15
electrical accessories	Buffer module
mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	517 015 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6EP34378SB000AY0