



SIMATIC NET, DP/AS-Interface Link 20 E, Gateway PROFIBUS DP/AS-Interface according to AS-Interface specification V 3.0 in degree of protection IP20

General technical data		
product designation		PROFIBUS DP/AS-Interface Link
product type designation		DP/AS-Interface Link 20E (AS-i V 3.0)
protection class IP		IP20
type of electrical connection of the AS-Interface		Screw-type connection
type of voltage supply		via AS-i
consumed current <ul style="list-style-type: none"> from profile conductors of the AS-Interface — at 30 V maximum 	mA	200
power loss [W]	W	4.5
insulation voltage rated value	V	500
product feature redundancy capability <ul style="list-style-type: none"> note 		Yes in connection with Y-Link
product function suitable for AS-i Power24V <ul style="list-style-type: none"> note 		No from product status 2 / firmware V3.1
product function <ul style="list-style-type: none"> web-based management diagnostics via email galvanic isolation 		No No Yes
display version <ul style="list-style-type: none"> as status display by LED 		PWR, APF, CER, AUP, CM, BF, SF
type of configuration of the AS-Interface		Set pushbutton on device, STEP7, GSD, command interface
Communication/ Protocol		
version of the AS-Interface specification		V 3.0
AS-Interface master profile is supported		M4 (in acc. with AS-interface specification V 3.0)
type of data transmission		PROFIBUS
number of interfaces <ul style="list-style-type: none"> as AS-Interface according to RS 485 according to Industrial Ethernet according to PROFINET according to wireless according to USB other 		1 1 0 0 0 0 0
product component optical interface		No
protocol is supported <ul style="list-style-type: none"> ASIsafe (Safety at work) protocol PROFIsafe protocol PROFIBUS protocol PROFINET IO protocol 		No No Yes No

• PROFINET CBA protocol		No
• TCP/IP		No
• SNMP		No
standard for wireless communication IEEE 802.11		No

Inputs/ Outputs

number of inputs for AS-Interface maximum		496
number of outputs for AS-Interface maximum		496
number of AS-i slaves per AS-Interface maximum		62
bus cycle time of the AS-Interface		
• for 31 slaves	ms	5
• for 62 slaves	ms	10
access to digital I/O data		via process image/peripheral addresses
access to analog I/O data		via data record transfer

Mechanical data

width	mm	90
height	mm	80
depth	mm	62
fastening method		snap-on fastening on 35 mm DIN rail
module format		IP20

Ambient conditions

ambient temperature		
• if installed on horizontal mounting rail during operation	°C	0 ... 60
• if installed on vertical mounting rail during operation	°C	0 ... 45
• during transport	°C	-40 ... +70
• during storage	°C	-40 ... +70
relative humidity at 25 °C during operation maximum	%	95
installation altitude at height above sea level maximum	m	2 000

Safety related data

suitability for use safety-related function		No
explosion protection marking for intrinsic safety of related equipment		
• EEx ia		No
• EEx ib		No
explosion protection category for gas		II 3 G Ex ec IIC T4 Gc
explosion protection category for dust		none

Certificates/ approvals

General Product Approval	EMC	For use in hazardous locations
--------------------------	-----	--------------------------------

[Confirmation](#)

[FM](#)



Declaration of Conformity	other
---------------------------	-------



[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=6GK1415-2AA10>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=6GK1415-2AA10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/6GK1415-2AA10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=6GK1415-2AA10&lang=en



last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK14152AA10