



SCALANCE XB116 unmanaged IE switch, 16x 10/100 Mbit/s RJ45 ports; for setting up small star and line topologies; LED diagnostics, IP20, Redundant power supply, 24 V AC/DC Manual available as a download .

<b>product type designation</b>		SCALANCE XB116
<b>transfer rate</b>		
transfer rate		10 Mbit/s, 100 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>		
number of electrical ports / maximum		16
<b>interfaces / for communication / integrated</b>		
number of electrical connections		
• for network components or terminal equipment		16; RJ45
<b>interfaces / other</b>		
number of electrical connections		
• for power supply		1
<b>supply voltage, current consumption, power loss</b>		
product component / connection for redundant voltage supply		Yes
<b>type of voltage / 1 / of the supply voltage</b>		DC
• supply voltage / 1 / rated value		24 V
• power loss [W] / 1 / rated value		4.8 W
• supply voltage / 1 / rated value		19.2 ... 28.8 V
• consumed current / 1 / maximum		0.2 A
• product component / 1 / fusing at power supply input		Yes
• fuse protection type / 1 / at input for supply voltage		0.6 A / 60 V
<b>type of voltage / 2 / of the supply voltage</b>		
• supply voltage / 2 / rated value		19.2 ... 28.8 V
<b>ambient conditions</b>		
ambient temperature		
• during operation		0 ... 60 °C
• during storage		-40 ... +80 °C
• during transport		-40 ... +80 °C
relative humidity		
• at 25 °C / without condensation / during operation / maximum		95 %
protection class IP		IP20
<b>design, dimensions and weights</b>		
design		compact
width		80 mm
height		117 mm
depth		109 mm
net weight		0.375 kg
fastening method		
• 35 mm top hat DIN rail mounting		Yes
• wall mounting		No

<ul style="list-style-type: none"> <li>• S7-300 rail mounting</li> <li>• S7-1500 rail mounting</li> </ul>	No No
<b>product functions / management, configuration, engineering</b>	
product function	
<ul style="list-style-type: none"> <li>• multiport mirroring</li> <li>• CoS</li> </ul>	No Yes
PROFINET conformity class	A
product function / switch-managed	No
<b>product functions / redundancy</b>	
product function	
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/operation in the PRP-network</li> <li>• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	Yes No
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>• for FM</li> <li>• for safety / from CSA and UL</li> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4 UL 60950-1, CSA C22.2 No. 60950-1 EN 61000-6-4 (Class B) 61000-6-2
MTBF	80 a
reference code	
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> <li>• according to IEC 81346-2:2019</li> </ul>	KF KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0:2009, EN60079-15:2010, II 3 G Ex nA IIC T4 Gc, KEMA 07ATEX0145 X
certificate of suitability	
<ul style="list-style-type: none"> <li>• IECEx</li> <li>• CCC / for hazardous zone according to GB standard</li> <li>• CCC / for hazardous zone according to GB standard / as marking</li> </ul>	Yes; IEC 60079-0, IEC 60079-15, IECEx DEK 14.0025X, Ex nA IIC T4 Gc Yes Ex nA IIC T4 Gc
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> <li>• KC approval</li> <li>• Regulatory Compliance Mark (RCM)</li> </ul>	Yes Yes
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAX-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a> . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a> . (V3.4)

last modified:

8/11/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK51160BA002AB2](#)