



SCALANCE XC116, Unmanaged IE switch, 16x 10/100 Mbit/s RJ45 ports, LED diagnostics, error-signaling contact with set pushbutton, redundant power supply Manual available as a download .

<b>product type designation</b>	<b>SCALANCE XC116</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	16
<b>interfaces / for communication / integrated</b>	
number of electrical connections	
• for network components or terminal equipment	16; RJ45
<b>interfaces / other</b>	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
<b>supply voltage, current consumption, power loss</b>	
product component / connection for redundant voltage supply	Yes
<b>type of voltage / 1 / of the supply voltage</b>	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	5.4 W
• consumed current / 1 / at rated supply voltage / maximum	0.45 A
• supply voltage / 1 / rated value	9.6 ... 31.2 V
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	2.5 A / 125 V
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	

design	compact
width	120 mm
height	147 mm
depth	125 mm
net weight	0.775 kg
material / of the enclosure	Polycarbonate (PC-GF10)
fastening method	
• 35 mm top hat DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
<b>product features, product functions, product components / general</b>	
number of automatically learnable MAC addresses	2048
<b>product functions / management, configuration, engineering</b>	
product function	
• multiport mirroring	No
• CoS	Yes
product function / switch-managed	No
product function	
• is supported / identification link	Yes
<b>product functions / redundancy</b>	
product function	
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
<b>standards, specifications, approvals</b>	
standard	
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for emitted interference	EN 61000-6-4 (Class B)
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0:2012 + A11:2013, EN60079-15:2010, II 3 G Ex nA IIC T4 Gc, KEMA 07ATEX0145 X, IEC 6079-0:2011, IEC 6079-0-15:2010
• from CSA and UL	UL 1604 and UL 2279-15 (Hazardous Location), Class 1 / Division 2 / Group A, B, C, D / T.., Class 1 / Zone 2 / Group IIC / T..
certificate of suitability	
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
<b>standards, specifications, approvals / other</b>	
laser protection class	LED Class 1
certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
• KC approval	Yes
• E1 approval	No
• EC Declaration of Conformity EN 61010, IEC 61010-1, UL 61010A-1	Yes
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	Yes
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• DNV GL	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Polski Rejestr Statkow (PRS)	Yes
• Royal Institution of Naval Architects (RINA)	Yes

#### further information / internet links

##### internet link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>  
<http://www.siemens.com/simatic-net>  
<https://mall.industry.siemens.com>  
<http://www.siemens.com/industry/infocenter>  
<http://automation.siemens.com/bilddb>  
<http://www.siemens.com/cax>  
<https://support.industry.siemens.com>

#### security information

##### security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

##### last modified:

8/18/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK51160BA002AC2](#)