



SCALANCE X202-2PIRT PRO, Managed IE IRT switch, Degree of protection IP65/67, 2x 10/100 Mbit/s Push Pull RJ45 ports, 2x 100 Mbit/s Push-pull SC-RJ port; Error signaling contact with set pushbutton, Redundant power supply, PROFINET IO device; network management, Redundancy Manager integrated, incl. electron. manual on CD-ROM, C-plug optional.

<b>product type designation</b>		<b>SCALANCE X202-2P IRT PRO</b>
<b>transfer rate</b>		
transfer rate		10 Mbit/s, 100 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>		
number of electrical ports / maximum		2
number of optical ports / maximum		2
<b>interfaces / for communication / integrated</b>		
number of electrical connections		
• for network components or terminal equipment		2
number of 100 Mbit/s SC-RJ-ports / for POF FOC		
• with push-pull connection system		2
<b>interfaces / other</b>		
number of electrical connections		
• for signaling contact		1
• for power supply		1
type of electrical connection		
• for signaling contact		5-pin M12 socket
• for power supply		5-pin push-pull plug PRO socket
design of the removable storage		
• C-PLUG		Yes
<b>signal inputs/outputs</b>		
operating voltage / of the signaling contacts		
• at DC / rated value		24 V
operational current / of the signaling contacts		
• at DC / maximum		0.1 A
<b>supply voltage, current consumption, power loss</b>		
<b>type of voltage / 1 / of the supply voltage</b>		DC
• supply voltage / 1 / rated value		24 V
• power loss [W] / 1 / rated value		7.2 W
• supply voltage / 1 / rated value		18 ... 32 V
• consumed current / 1 / maximum		0.3 A
• type of electrical connection / 1 / for power supply		5-pin Push Pull Plug PRO socket
• product component / 1 / fusing at power supply input		Yes
• fuse protection type / 1 / at input for supply voltage		1.1 A / 33 V
<b>ambient conditions</b>		
ambient temperature		
• during operation		-25 ... +60 °C
• during storage		-40 ... +70 °C
• during transport		-40 ... +70 °C
relative humidity		

<ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP65
<b>design, dimensions and weights</b>	
design	compact
width	90 mm
height	125 mm
depth	124 mm
net weight	1 kg
fastening method	
<ul style="list-style-type: none"> <li>• 35 mm top hat DIN rail mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• wall mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• S7-300 rail mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• S7-1500 rail mounting</li> </ul>	No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function	
<ul style="list-style-type: none"> <li>• CLI</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• web-based management</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• MIB support</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TRAPs via email</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• configuration with STEP 7</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• port mirroring</li> </ul>	No
<ul style="list-style-type: none"> <li>• multiport mirroring</li> </ul>	No
<ul style="list-style-type: none"> <li>• with IRT / PROFINET IO switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• PROFINET IO diagnosis</li> </ul>	Yes
PROFINET conformity class	C
network load class / according to PROFINET	2
product function / switch-managed	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• Telnet</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTPS</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TFTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• FTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• BOOTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• DCP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• LLDP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v1</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v2</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v3</li> </ul>	Yes
identification & maintenance function	
<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• I&amp;M1 - higher level designation/location designation</li> </ul>	Yes
<b>product functions / diagnostics</b>	
product function	
<ul style="list-style-type: none"> <li>• port diagnostics</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics Packet Size</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics packet type</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• error statistics</li> </ul>	Yes
<b>product functions / DHCP</b>	
product function	
<ul style="list-style-type: none"> <li>• DHCP client</li> </ul>	Yes
<b>product functions / redundancy</b>	
product function	
<ul style="list-style-type: none"> <li>• ring redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with redundancy</li> </ul>	Yes

manager	
<ul style="list-style-type: none"> <li>high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> <li>media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Parallel Redundancy Protocol (PRP)/operation in the PRP-network</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	No
<ul style="list-style-type: none"> <li>passive listening</li> </ul>	Yes
<b>product functions / security</b>	
protocol / is supported	
<ul style="list-style-type: none"> <li>SSH</li> </ul>	Yes
<b>product functions / time</b>	
product function	
<ul style="list-style-type: none"> <li>SICLOCK support</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>NTP</li> </ul>	No
<ul style="list-style-type: none"> <li>SNTP</li> </ul>	Yes
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>for FM</li> </ul>	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4, FM16US0205X
<ul style="list-style-type: none"> <li>for emitted interference</li> </ul>	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> <li>for interference immunity</li> </ul>	EN 61000-6-4:2001
MTBF	84.99 a
reference code	
<ul style="list-style-type: none"> <li>according to IEC 81346-2</li> </ul>	KF
<ul style="list-style-type: none"> <li>according to IEC 81346-2:2019</li> </ul>	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> <li>from CSA and UL</li> </ul>	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4, E240480
certificate of suitability	
<ul style="list-style-type: none"> <li>CCC / for hazardous zone according to GB standard</li> </ul>	Yes
<ul style="list-style-type: none"> <li>CCC / for hazardous zone according to GB standard / as marking</li> </ul>	Ex nA IIC T4 Gc
<ul style="list-style-type: none"> <li>for cULus HazLoc / as File Nr.</li> </ul>	E240480 (NWHF, NWHF7)
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-4:2001
<ul style="list-style-type: none"> <li>C-Tick</li> </ul>	Yes
<ul style="list-style-type: none"> <li>KC approval</li> </ul>	Yes
<ul style="list-style-type: none"> <li>railway application in accordance with EN 50155</li> </ul>	No
<ul style="list-style-type: none"> <li>railway application in accordance with EN 50124-1</li> </ul>	No
<b>accessories</b>	
product extension / optional / C-PLUG	Yes
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>to web page: selection aid TIA Selection Tool</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
<ul style="list-style-type: none"> <li>to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
<ul style="list-style-type: none"> <li>to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>to website: CAX-Download-Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or

---

networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

8/11/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52022JR002BA6](#)