



SCALANCE XF204-2BA managed IE switch, 4 x 10/100 Mbit/s, IEC 62443-4-2 certified; 2 x BusAdapter interface, error signaling contact, set pushbutton, redundant 24 V DC power supply, PROFINET device, extended temperature range -40 °C...+70 °C, conformal coating, with electr. manual on DVD, C-PLUG optional, supplied without BusAdapter

<b>product type designation</b>	<b>SCALANCE XF204-2BA</b>
product options	XF-200 base device without mounted BusAdapter
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	4
number of optical ports / maximum	2
<b>interfaces / for communication / integrated</b>	
number of electrical connections	
• for network components or terminal equipment	0
<b>interfaces / other</b>	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	2-pole terminal block
design of the removable storage	
• C-PLUG	Yes
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
<b>supply voltage, current consumption, power loss</b>	
product component / connection for redundant voltage supply	Yes
<b>type of voltage / 1 / of the supply voltage</b>	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	8.6 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	0.36 A
• type of electrical connection / 1 / for power supply	2-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	2.5 A (cannot be changed by user)
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	

<ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	compact
width	100 mm
height	117 mm
depth	74 mm
net weight	0.21 kg
fastening method	
<ul style="list-style-type: none"> <li>• 35 mm top hat DIN rail mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• wall mounting</li> </ul>	No
<ul style="list-style-type: none"> <li>• S7-300 rail mounting</li> </ul>	No
<ul style="list-style-type: none"> <li>• S7-1500 rail mounting</li> </ul>	No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function	
<ul style="list-style-type: none"> <li>• CLI</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• web-based management</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• MIB support</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TRAPs via email</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• configuration with STEP 7</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• port mirroring</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• multiport mirroring</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• PROFINET IO diagnosis</li> </ul>	Yes
PROFINET conformity class	B
network load class / according to PROFINET	2
product function / switch-managed	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• Telnet</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTPS</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TFTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• FTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• BOOTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• DCP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• LLDP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v1</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v2</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v3</li> </ul>	Yes
identification & maintenance function	
<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• I&amp;M1 - higher level designation/location designation</li> </ul>	Yes
<b>product functions / diagnostics</b>	
product function	
<ul style="list-style-type: none"> <li>• port diagnostics</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics Packet Size</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• statistics packet type</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• error statistics</li> </ul>	Yes
<b>product functions / VLAN</b>	
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
<b>product functions / DHCP</b>	
product function	
<ul style="list-style-type: none"> <li>• DHCP client</li> </ul>	Yes
<b>product functions / redundancy</b>	

product function	
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes
• Media Redundancy Protocol for Planned Duplication (MRPD)	No
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• redundancy procedure RSTP+	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	No
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
<b>product functions / security</b>	
protocol / is supported	
• SSH	Yes
<b>product functions / time</b>	
product function	
• SICLOCK support	No
protocol / is supported	
• NTP	No
• SNTP	Yes
<b>system modification during operation</b>	
product function / configuration in RUN via CiR/H-CiR	Yes
<b>standards, specifications, approvals</b>	
standard	
• for FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4, FM16US0205X
• for emitted interference	EN 61000-6-4:2001 (Class A)
• for interference immunity	EN 61000-6-2, EN 61000-6-4
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• from CSA and UL	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4, E223122
certificate of suitability	
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
• KC approval	Yes
• railway application in accordance with EN 50155	No
• railway application in accordance with EN 50124-1	No
<b>standards, specifications, approvals / marine classification</b>	

Marine classification association	
• French marine classification society (BV)	Yes
• Korean Register of Shipping (KRS)	Yes
<b>accessories</b>	
product extension / optional / C-PLUG	Yes
<b>further information / internet links</b>	
internet link	
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to website: Industrial communication	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAX-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a> . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a> . (V3.4)

last modified:

8/11/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52042AA002GF2](#)