

SCALANCE XR324-4M EEC; Managed IE switch, 19" rack; 16x 10/100/1000 Mbit/s for RJ45 ports electrical; 4x 100/1000 Mbit/s for 2-port media modules, electrical or optical; LED diagnostics; error signaling Contact; Select/set pushbutton, PROFINET IO device, network management, Integrated redundancy manager; Power supply 1x 24 V DC; Ports in the front.



Figure similar

product type designation		SCALANCE XR324-4M EEC
transfer rate		
transfer rate		10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices		
number of electrical ports / maximum		24
number of optical ports / maximum		8
interfaces / for communication / integrated		
number of electrical connections		16; RJ45
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>		
number of 100 Mbit/s ST(BFOC) ports		8
<ul style="list-style-type: none"> <li>for multimode</li> </ul>		
number of 100 Mbit/s SC ports		8
<ul style="list-style-type: none"> <li>for multimode</li> </ul>		
number of 1000 Mbit/s LC ports		8
<ul style="list-style-type: none"> <li>for multimode</li> <li>for single mode (LD)</li> </ul>		8
interfaces / other		
number of electrical connections		1
<ul style="list-style-type: none"> <li>for operator console</li> <li>for signaling contact</li> <li>for media module</li> <li>for power supply</li> </ul>		1 4 1
type of electrical connection		RJ11 2-pole terminal block 4-pole terminal block
<ul style="list-style-type: none"> <li>for operator console</li> <li>for signaling contact</li> <li>for power supply</li> </ul>		
design of the removable storage		Yes
<ul style="list-style-type: none"> <li>C-PLUG</li> </ul>		
signal inputs/outputs		
operating voltage / of the signaling contacts		24 V
<ul style="list-style-type: none"> <li>at DC / rated value</li> </ul>		
operational current / of the signaling contacts		0.1 A
<ul style="list-style-type: none"> <li>at DC / maximum</li> </ul>		
supply voltage, current consumption, power loss		
type of voltage supply / redundant power supply unit		No
type of voltage / 1 / of the supply voltage		DC
<ul style="list-style-type: none"> <li>supply voltage / 1 / rated value</li> <li>power loss [W] / 1 / rated value</li> <li>supply voltage / 1 / rated value</li> </ul>		24 V 40 W 19.2 ... 57.6 V

<ul style="list-style-type: none"> <li>consumed current / 1 / maximum</li> <li>type of electrical connection / 1 / for power supply</li> <li>product component / 1 / fusing at power supply input</li> </ul>	1.6 A 4-pole terminal block Yes
<b>ambient conditions</b>	
ambient temperature <ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> <li>during transport</li> <li>note</li> </ul>	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C Extended temperature upper limit of +85° C permitted for 16 hours. Reduced operating temperature through the use of media modules (-40 °C to +70 °C) or SFP plug-in transceivers (-40 °C to +60 °C)
relative humidity <ul style="list-style-type: none"> <li>at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	19" rack
number of modular height units / relating to 19-inch cabinet	1
width	483 mm
height	44 mm
depth	305 mm
net weight	6.5 kg
fastening method <ul style="list-style-type: none"> <li>19-inch installation</li> <li>35 mm top hat DIN rail mounting</li> <li>wall mounting</li> <li>S7-300 rail mounting</li> <li>S7-1500 rail mounting</li> </ul>	When used in shipbuilding, the device must be secured in the 19" rack at four points Yes No No No No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	100
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function <ul style="list-style-type: none"> <li>CLI</li> <li>web-based management</li> <li>MIB support</li> <li>TRAPs via email</li> <li>configuration with STEP 7</li> <li>RMON</li> <li>port mirroring</li> <li>multiport mirroring</li> <li>CoS</li> <li>PROFINET IO diagnosis</li> </ul>	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
PROFINET conformity class	B
product function / switch-managed	Yes
protocol / is supported <ul style="list-style-type: none"> <li>Telnet</li> <li>HTTP</li> <li>HTTPS</li> <li>TFTP</li> <li>FTP</li> <li>BOOTP</li> <li>GMRP</li> <li>DCP</li> <li>LLDP</li> <li>SNMP v1</li> <li>SNMP v2</li> <li>SNMP v3</li> <li>IGMP (snooping/querier)</li> </ul>	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
identification & maintenance function	

• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
<b>product functions / diagnostics</b>	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
<b>product functions / VLAN</b>	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
<b>product functions / DHCP</b>	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
<b>product functions / redundancy</b>	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
<b>product functions / security</b>	
product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
<b>product functions / time</b>	
product function	

<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 1588 profile default</li> </ul>	Yes
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>• for FM</li> </ul>	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-1-03
<ul style="list-style-type: none"> <li>• for emitted interference</li> </ul>	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> <li>• for interference immunity</li> </ul>	EN 61000-6-2:2005
MTBF	15 a
reference code	
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> </ul>	KF
<ul style="list-style-type: none"> <li>• according to IEC 81346-2:2019</li> </ul>	KFE
<b>standards, specifications, approvals / CE</b>	
certificate of suitability / CE marking	Yes
standard	
<ul style="list-style-type: none"> <li>• for EMC</li> </ul>	IEC 61850, IEEE 1613
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> <li>• from CSA and UL</li> </ul>	ANSI / ISA 12.12.01, CSA C22.2 No. 142-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
certificate of suitability	
<ul style="list-style-type: none"> <li>• CCC / for hazardous zone according to GB standard</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• CCC / for hazardous zone according to GB standard / as marking</li> </ul>	Ex nA IIC T4 Gc
<b>standards, specifications, approvals / other</b>	
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> <li>• C-Tick</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• KC approval</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEC 61850-3</li> </ul>	Yes
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
<ul style="list-style-type: none"> <li>• Korean Register of Shipping (KRS)</li> </ul>	Yes
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
<ul style="list-style-type: none"> <li>• to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>• to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>• to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
<ul style="list-style-type: none"> <li>• to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>• to website: CAX-Download-Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>• to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a> . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a> . (V3.4)

last modified:

8/11/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK53244GG101ER2](#)