

SCALANCE XR324-4M EEC; Managed IE switch, 19" rack; 16x 10/100/1000 Mbit/s for RJ45 ports electrical; 4x 100/1000 Mbit/s for 2-port media modules, electrical or optical; LED diagnostics; error signaling Contact; Select/set pushbutton, PROFINET IO device, network management, Integrated redundancy manager; Power supply 2x 230 V AC; Ports in the front.



product type designation	SCALANCE XR324-4M EEC
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	24
number of optical ports / maximum	8
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	16; RJ45
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	8
number of 100 Mbit/s SC ports	
• for multimode	8
number of 1000 Mbit/s LC ports	
• for multimode	8
• for single mode (LD)	8
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for media module	4
• for power supply	2
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2 x 3-pole terminal block
• for power supply	2 x 3-pole terminal block
design of the removable storage	
• C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	
• at AC / rated value	276 V
• at DC / rated value	230 V
operational current / of the signaling contacts	
• at AC / maximum	5 A
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
type of voltage supply / redundant power supply unit	Yes
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	230 V
• power loss [W] / 1 / rated value	42 W

<ul style="list-style-type: none"> • supply voltage / 1 / rated value • consumed current / 1 / maximum • type of electrical connection / 1 / for power supply • product component / 1 / fusing at power supply input • fuse protection type / 1 / at input for supply voltage 	80 ... 276 V 0.7 A 2 x 3-pole terminal block Yes 3.15 A / 250 V
type of voltage / 2 / of the supply voltage <ul style="list-style-type: none"> • power loss [W] / 2 / rated value • consumed current / 2 / at rated supply voltage / maximum • supply voltage / 2 / rated value • type of electrical connection / 2 / for power supply • product component / 2 / fusing at power supply input 	DC 42 W 0.7 A 60 ... 250 V 2 x 3-pole terminal block Yes
ambient conditions	
ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport • note 	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C Extended temperature upper limit of +85° C permitted for 16 hours. Reduced operating temperature through the use of media modules (-40 °C to +70 °C) or SFP plug-in transceivers (-40 °C to +60 °C)
relative humidity <ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	19" rack
number of modular height units / relating to 19-inch cabinet	1
width	483 mm
height	44 mm
depth	305 mm
net weight	7 kg
fastening method <ul style="list-style-type: none"> • 19-inch installation • 35 mm top hat DIN rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting 	When used in shipbuilding, the device must be secured in the 19" rack at four points Yes No No No No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	100
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function <ul style="list-style-type: none"> • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • RMON • port mirroring • multiport mirroring • CoS • PROFINET IO diagnosis 	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
PROFINET conformity class	B
product function / switch-managed	Yes
protocol / is supported <ul style="list-style-type: none"> • Telnet • HTTP • HTTPS • TFTP • FTP • BOOTP 	Yes Yes Yes Yes Yes Yes

• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
product functions / security	
product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes

<ul style="list-style-type: none"> • broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes
<ul style="list-style-type: none"> • IEEE 1588 profile default 	Yes
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 508, CSA C22.2 No. 142-M1987
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2:2005
MTBF	20 a
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	KF
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
standard	
<ul style="list-style-type: none"> • for EMC 	IEC 61850, IEEE 1613
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	-
<ul style="list-style-type: none"> • from CSA and UL 	No
standards, specifications, approvals / other	
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • IEC 61850-3 	Yes
standards, specifications, approvals / marine classification	
Marine classification association	
<ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
<ul style="list-style-type: none"> • Korean Register of Shipping (KRS) 	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com . (V3.4)

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK53244GG104ER2](#)