



PE408PoE Port Extender for SCALANCE XM-400 managed modular IE switch; extension by 8x 10/100/1000 Mbit/s RJ45 with up to 8 ports PoE according to IEEE802.3AT; for PoE separate power supply required.

| | |
|---|------------------------------------|
| product type designation | SCALANCE PE408PoE |
| transfer rate | |
| transfer rate | 10 Mbit/s, 100 Mbit/s, 1000 Mbit/s |
| interfaces / for communication / maximum configuration for modular devices | |
| number of electrical ports / maximum | 8 |
| number of electrical ports / with PoE / maximum | 8 |
| interfaces / for communication / integrated | |
| number of electrical connections | |
| • for network components or terminal equipment | 8 |
| • for Power-over-Ethernet / for network components or terminal equipment | 8 |
| number of 10/100/1000 Mbit/s RJ45 ports / integrated | |
| • with securing collar / with PoE | 8 |
| interfaces / other | |
| type of electrical connection | |
| • for power supply | 2-pole terminal block |
| number of extender expansion interfaces | 2 |
| product feature / hot-swappable interface modules | Yes |
| supply voltage, current consumption, power loss | |
| product component / connection for redundant voltage supply | Yes |
| supplied active power / of PSE / with PoE | |
| • per port / maximum | 30 W |
| • total / maximum | 180 W |
| type of voltage / 1 / of the supply voltage | DC |
| • supply voltage / 1 / rated value | 54 V |
| • power loss [W] / 1 / rated value | 4.8 W |
| • supply voltage / 1 / rated value | 51.3 ... 56.7 V |
| • consumed current / 1 / maximum | 0.2 A |
| • type of electrical connection / 1 / for power supply | 2-pole terminal block |
| • product component / 1 / fusing at power supply input | Yes |
| • fuse protection type / 1 / at input for supply voltage | F 4 A / 60 V |
| ambient conditions | |
| ambient temperature | |
| • during operation | -40 ... +60 °C |
| • during storage | -40 ... +85 °C |
| • during transport | -40 ... +85 °C |
| relative humidity | |
| • at 25 °C / without condensation / during operation / maximum | 95 % |
| protection class IP | IP20 |

| | |
|--|---|
| design, dimensions and weights | |
| design | SIMATIC S7-1500 device design |
| width | 70 mm |
| height | 147 mm |
| depth | 125 mm |
| net weight | 0.65 kg |
| fastening method | |
| • 19-inch installation | No |
| • 35 mm top hat DIN rail mounting | Yes |
| • wall mounting | No |
| • S7-300 rail mounting | Yes |
| • S7-1500 rail mounting | Yes |
| product functions / management, configuration, engineering | |
| PROFINET conformity class | B |
| standards, specifications, approvals | |
| standard | |
| • for FM | FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4 |
| • for safety / from CSA and UL | UL 508, UL 60950-1, CSA C22.2 Nr. 60950-1-03 |
| • for emitted interference | EN 61000-6-4 (Class A) |
| • for interference immunity | EN 61000-6-2 |
| reference code | |
| • according to IEC 81346-2 | KF |
| • according to IEC 81346-2:2019 | KFE |
| standards, specifications, approvals / CE | |
| certificate of suitability / CE marking | Yes |
| standards, specifications, approvals / hazardous environments | |
| standard / for hazardous zone | EN 60079-0: 2009, EN60079-15: 2010, II 3 G Ex nA IIC T4 Gc, KEMA 07 ATEX 0145 X, IECEx DEK 14.0025X |
| • from CSA and UL | ISA 12.12.01-2012 (Hazardous Location), Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4 |
| certificate of suitability | |
| • CCC / for hazardous zone according to GB standard | Yes |
| • CCC / for hazardous zone according to GB standard / as marking | Ex nA IIC T4 Gc |
| standards, specifications, approvals / other | |
| certificate of suitability | EN 61000-6-2, EN 61000-6-4 |
| • C-Tick | Yes |
| • KC approval | Yes |
| • railway application in accordance with EN 50121-4 | Yes |
| standards, specifications, approvals / marine classification | |
| Marine classification association | |
| • American Bureau of Shipping Europe Ltd. (ABS) | Yes |
| • French marine classification society (BV) | Yes |
| • Det Norske Veritas (DNV) | No |
| • Germanische Lloyd (GL) | No |
| • DNV GL | Yes |
| • Lloyds Register of Shipping (LRS) | Yes |
| • Nippon Kaiji Kyokai (NK) | Yes |
| • Polski Rejestr Statkow (PRS) | Yes |
| • Royal Institution of Naval Architects (RINA) | Yes |
| further information / internet links | |
| internet link | |
| • to web page: selection aid TIA Selection Tool | http://www.siemens.com/tia-selection-tool |
| • to website: Industrial communication | http://www.siemens.com/simatic-net |
| • to website: Industry Mall | https://mall.industry.siemens.com |
| • to website: Information and Download Center | http://www.siemens.com/industry/infocenter |
| • to website: Image database | http://automation.siemens.com/bilddb |
| • to website: CAX-Download-Manager | http://www.siemens.com/cax |
| • to website: Industry Online Support | https://support.industry.siemens.com |
| security information | |

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

8/18/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK54080PA008AP2](#)