

SCALANCE XR552-12M; managed IE switch; 19" rack; 4x 1000/10000 Mbit/s SFP+; 12x 100/1000 Mbit/s 4-port media modules, electrical, electrical PoE or optical; LED diagnostics; error signaling contact; Select/set pushbutton, PROFINET IO device, network management, integrated redundancy manager; office features (RSTP, VLAN, IGMP, ...); C-plug in scope of delivery Layer 3 prepared; ports in the front.



product type designation	SCALANCE XR552-12M
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s, 10 Gbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	48
number of optical ports / maximum	52
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	RJ45
• for Power-over-Ethernet / for network components or terminal equipment	12
number of electrical connections	
• for SFP+	4
interfaces / for communication / plug-in	
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	48
• for single mode (LD)	48
number of 1000 Mbit/s SC ports	
• for multimode	48
• for single mode (LD)	48
number of electrical connections	
• for SFP	4
• for SFP+	4
interfaces / other	
number of electrical connections	
• for operator console	1
• for management purposes	1
• for signaling contact	1
• for media module	12
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for management purposes	RJ45
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG/KEY-PLUG	Yes
product feature / hot-swappable interface modules	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	

• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
type of voltage supply / redundant power supply unit	No
supplied active power / of PSE / with PoE	
• per port / maximum	30 W
• total / maximum	180 W
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	34.08 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	12.5 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
• note	Operation with integral fan, replaceable
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	19" rack
number of modular height units / relating to 19-inch cabinet	3
width	449 mm
height	130.8 mm
depth	305 mm
net weight	10 kg
fastening method	
• 19-inch installation	Yes
• 35 mm top hat DIN rail mounting	No
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
type of cable outlet	Cable outlet at front
product features, product functions, product components / general	
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	9216 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes

• FTP	Yes
• BOOTP	Yes
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	Yes
• VLAN - IP-based	Yes
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / routing	
service / routing / note	IP routing in combination with KEY-PLUG XR-500
product function	
• static IP routing	Yes
• static IP routing IPv6	Yes
• dynamic IP routing	Yes
• dynamic IP routing IPv6	Yes
protocol / is supported	
• RIPv2	Yes
• RIPnG for IPv6	Yes
• OSPFv2	Yes
• OSPFv3 for IPv6	Yes
• VRRP	Yes
• VRRP for IPv6	Yes
product functions / redundancy	
product function	
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes

<ul style="list-style-type: none"> • redundancy procedure STP • redundancy procedure RSTP • redundancy procedure RSTP+ • redundancy procedure MSTP • Parallel Redundancy Protocol (PRP)/operation in the PRP-network • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) • passive listening 	Yes Yes Yes Yes Yes No Yes
protocol / is supported	
<ul style="list-style-type: none"> • LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> • ACL - MAC-based • ACL - port/MAC-based • IEEE 802.1x (radius) • broadcast/multicast/unicast limiter • broadcast blocking 	Yes Yes Yes Yes Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP • SNTP 	Yes Yes
type of time synchronization	IEEE 1588
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for FM • for safety / from CSA and UL • for emitted interference • for interference immunity 	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4 UL 60950-1, CSA C22.2 No. 60950-1-03 EN 61000-6-4 (Class A) EN 61000-6-2
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	KF KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-0: 2009, EN60079-15: 2010, II 3 G Ex nA IIC T4 Gc, KEMA 07 ATEX 0145 X
<ul style="list-style-type: none"> • from CSA and UL 	ISA 12.12.01-2012 (Hazardous Location), Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4
certificate of suitability	
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking 	Yes Ex nA IIC T4 Gc
standards, specifications, approvals / other	
certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> • C-Tick • KC approval • E1 approval • E1 approval 	Yes Yes No No
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax

security information

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

8/18/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK55520AA002AR2](#)