

product type designation



W734-1 RJ45 (USA) (x20)

IWLAN client, pack of 20, SCALANCE W734-1, RJ45, 1 radio, 2 R-SMA antenna port, iFeatures support via key plug, IEEE 802.11a/b/g/h/n, 2.4/5GHz, gross data rate 300 Mbit/s, 2x RJ45 max. 100 Mbit/s, PoE integrated 2-port switch, redundant 24 V DC, terminal block, IP30, -20... 60 °C, plug slot WPA2/802.11i/e, observe national approvals! CERT ID: MSN-W1-RJ-E2, scope of delivery: Manuals on CD-ROM, German/English, 1x terminal block; only for operation in USA 1 pack = 20 units

transfer rate

transfer rate	
• with WLAN / maximum	300 Mbit/s
• for Industrial Ethernet	10, 100 Mbit/s
transfer rate / for Industrial Ethernet	
• minimum	10 Mbit/s
• maximum	100 Mbit/s

interfaces

number of electrical connections	
• for network components or terminal equipment	2
• for power supply	1
• for redundant voltage supply	1
type of electrical connection	
• for network components or terminal equipment	RJ45 socket
• for power supply	4-pole screw terminal, PoE
design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes

memory

design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes

interfaces / wireless

number of radio cards / permanently installed	1
transmission mode / for multiple input multiple output (MIMO)	2x2
number of spatial streams	2
number of electrical connections / for external antenna(s)	2
type of electrical connection / for external antenna(s)	R-SMA (socket)
product feature / external antenna can be mounted directly on device	Yes

supply voltage, current consumption, power loss

type of voltage / of the supply voltage	DC
supply voltage	
• from Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af	48 V
consumed current	
• at DC / at 24 V / typical	0.25 A
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.125 A
power loss [W]	

<ul style="list-style-type: none"> • at DC / at 24 V / typical • with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical 	6 W
	6 W
supply voltage / 1	
<ul style="list-style-type: none"> • from terminal block 	19.2 V
supply voltage / 2	
<ul style="list-style-type: none"> • from terminal block 	28.8 V
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport 	-20 ... +60 °C
	-40 ... +85 °C
	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W774-1 RJ45 or W734-1 RJ45 product must be installed in an enclosure. To comply with EN 50021, this enclosure must meet the requirements of at least IP 54 in compliance with EN 60529.
protection class IP	IP30
design, dimensions and weights	
width	26 mm
height	156 mm
depth	127 mm
width / of the enclosure / without antenna	26 mm
height / of the enclosure / without antenna	147 mm
depth / of the enclosure / without antenna	127 mm
net weight	0.52 kg
fastening method	wall mounting only if flat mounted
<ul style="list-style-type: none"> • S7-300 rail mounting • S7-1500 rail mounting • 35 mm top hat DIN rail mounting • wall mounting 	Yes
	Yes
	Yes
	Yes
radio frequencies	
operating frequency	
<ul style="list-style-type: none"> • for WLAN in 2.4 GHz frequency band • for WLAN in 5 GHz frequency band 	2.41 ... 2.48 GHz; depending on the country approvals
	4.9 ... 5.8 GHz; depending on the country approvals
product features, product functions, product components / general	
product function / Access Point Mode	No
product function / client Mode	Yes
product function	
<ul style="list-style-type: none"> • iPCF client • iPCF-MC client 	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
	Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	1
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures' only
product functions / management, configuration, engineering	
number of manageable IP addresses / in client	8
product function	
<ul style="list-style-type: none"> • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • configuration with STEP 7 in the TIA Portal • WDS 	Yes
	Yes
	Yes
	Yes
	Yes
	Yes
	No
protocol / is supported	
<ul style="list-style-type: none"> • Address Resolution Protocol (ARP) • ICMP • Telnet • HTTP • HTTPS 	Yes
	Yes
	Yes
	Yes
	Yes

<ul style="list-style-type: none"> • TFTP • DCP • LLDP 	Yes Yes No
identification & maintenance function	
<ul style="list-style-type: none"> • I&M0 - device-specific information • I&M1 - higher level designation/location designation 	Yes Yes
product functions / diagnostics	
product function	
<ul style="list-style-type: none"> • PROFINET IO diagnosis • link check • connection monitoring IP-Alive • SysLog 	Yes No No Yes
protocol / is supported	
<ul style="list-style-type: none"> • SNMP v1 • SNMP v2 • SNMP v3 	Yes Yes Yes
product functions / VLAN	
product function	
<ul style="list-style-type: none"> • function VLAN with IWLAN 	No
product functions / DHCP	
product function	
<ul style="list-style-type: none"> • DHCP client • DHCP server • DHCP Option 82 	Yes Yes Yes
product functions / redundancy	
protocol / is supported	
<ul style="list-style-type: none"> • STP/RSTP • MSTP • RSTP 	Yes Yes Yes
product functions / security	
product function	
<ul style="list-style-type: none"> • ACL - MAC-based • management security, ACL-IP based • IEEE 802.1x (radius) • NAT/NAPT • access protection according to IEEE802.11i • WPA/WPA2 • TKIP/AES 	Yes Yes Yes Yes Yes Yes Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH • RADIUS 	Yes Yes
product functions / time	
protocol / is supported	
<ul style="list-style-type: none"> • NTP • SNTP • SIMATIC time synchronization (SIMATIC Time) 	Yes Yes Yes
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for FM • for safety / from CSA and UL 	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4 UL 60950-1, CSA C22.2 No. 60950-1
certificate of suitability	
<ul style="list-style-type: none"> • EC Declaration of Conformity • CE marking • C-Tick • E1 approval • railway application in accordance with EN 50155 • NEMA TS2 • IEC 61375 • IEC 61850-3 • NEMA4X 	Yes Yes Yes No No No No No No

<ul style="list-style-type: none"> • Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af 	Yes
<ul style="list-style-type: none"> • Power-over-Ethernet according to IEEE802.3at for type 2 	Yes
standard for wireless communication	
<ul style="list-style-type: none"> • IEEE 802.11a 	Yes
<ul style="list-style-type: none"> • IEEE 802.11b 	Yes
<ul style="list-style-type: none"> • IEEE 802.11e 	Yes
<ul style="list-style-type: none"> • IEEE 802.11g 	Yes
<ul style="list-style-type: none"> • IEEE 802.11h 	Yes
<ul style="list-style-type: none"> • IEEE 802.11i 	Yes
<ul style="list-style-type: none"> • IEEE 802.11n 	Yes
wireless approval	You will find the current list of countries at: www.siemens.de/funkzulassungen
standards, specifications, approvals / marine classification	
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	Yes
<ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
<ul style="list-style-type: none"> • DNV GL 	Yes
<ul style="list-style-type: none"> • Korean Register of Shipping (KRS) 	Yes
<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) 	Yes
<ul style="list-style-type: none"> • Nippon Kaiji Kyokai (NK) 	Yes
<ul style="list-style-type: none"> • Polski Rejestr Statkow (PRS) 	Yes
<ul style="list-style-type: none"> • Royal Institution of Naval Architects (RINA) 	Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
accessories	
accessories	24 V DC screw terminal included in scope of delivery
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to website: TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to the website: IWLAN 	http://www.siemens.com/iwlan
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com . (V3.4)

last modified:

10/12/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57341FX000AB6