

### product type designation



### W786-2 RJ45

IWLAN Access Point, SCALANCE W786-2 RJ45, 2 radios, 6 R-SMA antenna port, iFeatures support via key plug, IEEE 802.11a/b/g/h/n, 2.4/5GHz, gross 450 Mbit/s per radio, 1x RJ45 max. 1 Gbit/s, PoE, redundant 24 V DC, terminal block, 110 - 230 V AC via PS791-2AC IP65, -40...+60 °C, plug slot, WPA2/802.11i/e, observe national approvals! CERT ID: EAPN-W2-RJ-E3, includes: MPCIE-R1-ABGN-U3, scope of delivery: Manuals on CD-ROM, German/English, 1x terminal block; for operation outside of USA/Israel

### transfer rate

transfer rate	
• with WLAN / maximum	450 Mbit/s
• for Industrial Ethernet	10, 1000, 1000 Mbit/s
transfer rate / for Industrial Ethernet	
• minimum	10 Mbit/s
• maximum	1000 Mbit/s

### interfaces

number of electrical connections	
• for network components or terminal equipment	1
• for power supply	1
• for redundant voltage supply	1
type of electrical connection	
• for network components or terminal equipment	RJ45 socket
• for power supply	2-pole connector (24 V DC) or optionally available power supply adapter (4-pole 24 V DC or 3-pole 110 to 230 V AC)
design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes

### memory

design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes

### interfaces / wireless

number of radio cards / permanently installed	2
transmission mode / for multiple input multiple output (MIMO)	3x3
number of spatial streams	3
number of electrical connections / for external antenna(s)	6
type of electrical connection / for external antenna(s)	R-SMA (socket)
product feature / external antenna can be mounted directly on device	No

### supply voltage, current consumption, power loss

type of voltage / of the supply voltage	DC
supply voltage	
• from Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af	48 V
• from Power-over-Ethernet according to IEEE802.3at for type 2	50 V
• from optional integrable power supply	
— at AC	100 ... 240 V

— at DC	12 ... 24 V
consumed current	
• at DC / at 24 V / typical	0.63 A
• at AC / at 230 V / typical	0.07 A
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.22 A
power loss [W]	
• at DC / at 24 V / typical	15 W
• at AC / at 230 V / typical	15 W
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	10.7 W
<b>supply voltage / 1</b>	
• from terminal block	19.2 V
<b>supply voltage / 2</b>	
• from terminal block	28.8 V
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +70 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	100 %
ambient condition / for operation	When using the 100 - 240 V AC power supply, an operating temperature of -40 °C to +60 °C is permissible
protection class IP	IP65
<b>design, dimensions and weights</b>	
width / of the enclosure / without antenna	251 mm
height / of the enclosure / without antenna	251 mm
depth / of the enclosure / without antenna	72 mm
net weight	2.24 kg
fastening method	For mast mounting, 35 mm DIN rail mounting and S7-300 rail mounting, an additional support plate is required
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	No
• 35 mm top hat DIN rail mounting	Yes
• wall mounting	Yes
<b>radio frequencies</b>	
operating frequency	
• for WLAN in 2.4 GHz frequency band	2.41 ... 2.48 GHz; depending on the country approvals
• for WLAN in 5 GHz frequency band	4.9 ... 5.8 GHz; depending on the country approvals
<b>product features, product functions, product components / general</b>	
product function / Access Point Mode	Yes
product function / client Mode	Yes
number of SSIDs	16
product function	
• iPCF Access Point	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures'
• iPCF client	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
• iPCF-MC Access Point	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures'
• iPCF-MC client	Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	2
product function / iREF	Yes; In combination only with 'KEY-PLUG W780 iFeatures'
number of iREF-capable radio modules	2
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' only
<b>product functions / management, configuration, engineering</b>	
number of manageable IP addresses / in client	8
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes

<ul style="list-style-type: none"> <li>• configuration with STEP 7</li> <li>• configuration with STEP 7 in the TIA Portal</li> <li>• operation with IWLAN controller</li> <li>• operation with Enterasys WLAN controller</li> <li>• forced roaming on IP down with IWLAN</li> <li>• forced roaming on link down with IWLAN</li> <li>• WDS</li> </ul>	Yes Yes No No Yes Yes Yes
protocol / is supported <ul style="list-style-type: none"> <li>• Address Resolution Protocol (ARP)</li> <li>• ICMP</li> <li>• Telnet</li> <li>• HTTP</li> <li>• HTTPS</li> <li>• TFTP</li> <li>• DCP</li> <li>• LLDP</li> </ul>	Yes Yes Yes Yes Yes Yes Yes Yes
identification & maintenance function <ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> <li>• I&amp;M1 - higher level designation/location designation</li> </ul>	Yes Yes
<b>product functions / diagnostics</b>	
product function <ul style="list-style-type: none"> <li>• PROFINET IO diagnosis</li> <li>• link check</li> <li>• connection monitoring IP-Alive</li> <li>• localization via Aeroscout</li> <li>• SysLog</li> </ul>	Yes No No Yes Yes
protocol / is supported <ul style="list-style-type: none"> <li>• SNMP v1</li> <li>• SNMP v2</li> <li>• SNMP v3</li> </ul>	Yes Yes Yes
<b>product functions / VLAN</b>	
product function <ul style="list-style-type: none"> <li>• function VLAN with IWLAN</li> </ul>	Yes
<b>product functions / DHCP</b>	
product function <ul style="list-style-type: none"> <li>• DHCP client</li> <li>• DHCP server</li> <li>• DHCP Option 82</li> </ul>	Yes Yes Yes
<b>product functions / redundancy</b>	
protocol / is supported <ul style="list-style-type: none"> <li>• STP/RSTP</li> <li>• MSTP</li> <li>• RSTP</li> </ul>	Yes Yes Yes
<b>product functions / security</b>	
product function <ul style="list-style-type: none"> <li>• ACL - MAC-based</li> <li>• management security, ACL-IP based</li> <li>• IEEE 802.1x (radius)</li> <li>• NAT/NAPT</li> <li>• access protection according to IEEE802.11i</li> <li>• WPA/WPA2</li> <li>• TKIP/AES</li> </ul>	Yes Yes Yes No Yes Yes Yes
protocol / is supported <ul style="list-style-type: none"> <li>• SSH</li> <li>• RADIUS</li> </ul>	Yes Yes
<b>product functions / time</b>	
protocol / is supported <ul style="list-style-type: none"> <li>• NTP</li> <li>• SNTP</li> <li>• SIMATIC time synchronization (SIMATIC Time)</li> </ul>	Yes Yes Yes

**standards, specifications, approvals**

standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X
certificate of suitability	
• EC Declaration of Conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• E1 approval	Yes
• railway application in accordance with EN 50155	No
• railway application in accordance with EN 50121-4	Yes
• NEMA TS2	No
• IEC 61375	No
• IEC 61850-3	No
• NEMA4X	Yes
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	Yes
• Power-over-Ethernet according to IEEE802.3at for type 2	Yes
standard for wireless communication	
• IEEE 802.11a	Yes
• IEEE 802.11b	Yes
• IEEE 802.11e	Yes
• IEEE 802.11g	Yes
• IEEE 802.11h	Yes
• IEEE 802.11i	Yes
• IEEE 802.11n	Yes
wireless approval	You will find the current list of countries at: <a href="http://www.siemens.de/funkzulassungen">www.siemens.de/funkzulassungen</a>

**standards, specifications, approvals / marine classification**

Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	Yes
• DNV GL	Yes
• Korean Register of Shipping (KRS)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	Yes
• Royal Institution of Naval Architects (RINA)	Yes

**standards, specifications, approvals / hazardous environments**

standard / for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes
• as marking	Ex nA IIC T4 Gc

**accessories**

accessories	24 V DC screw terminal included in scope of delivery
-------------	--

**further information / internet links**

internet link	
• to website: TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to the website: IWLAN	<a href="http://www.siemens.com/iwlan">http://www.siemens.com/iwlan</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAX-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**security information**

security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly
----------------------	--

---

check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

**last modified:**

5/27/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57862FC000AA0