

product type designation



IWLAN terminating resistor TI795-1R RSMA Male

R-SMA male termination Impedance TI795-1R 2.4 and 5 GHz, IP65, 0...6 GHz; 1 pack=3 units.

electrical data

number of electrical connections	1
type of electrical connection	R-SMA male
transmission frequency	0 ... 6 GHz
impedance	50 Ω
return loss / minimum	25 dB

ambient conditions

ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
protection class IP	IP65

design, dimensions and weights

diameter	9 mm
length	15 mm
net weight	5 g

standards, specifications, approvals

certificate of suitability	
• RoHS conformity	Yes

further information / internet links

internet link	
• to website: TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/snst
• to the website: IWLAN	http://www.siemens.com/iwlan
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mail	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/20/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57951TR100AA6