

product type designation




Power Supply SCALANCE PS9230 PoE

SCALANCE PS9230PoE power supply for Power over Ethernet, input: 120/230 V AC, output: 54 V DC/1.6 A NEC Class 2.

type of current supply	Input: AC 120 / 230 V, Output: DC 54 V / 1.6 A, NEC CLASS 2
suitability for use	Power supply for PoE
electrical data / input	
voltage curve / at input	AC single phase
supply voltage / rated value	230 V
supply voltage / rated value	85 ... 264 V
type of voltage / of the supply voltage	AC
consumed current / at rated supply voltage / maximum	1 A
design of input / wide range input	Yes
overvoltage category	Category II
buffering time / for rated value of the output current / in the event of power failure / minimum	50 ms
line frequency	
• 50 Hz	Yes
• 60 Hz	Yes
• 1 / rated value	50 Hz
• 2 / rated value	60 Hz
line frequency	47 ... 63 Hz
input current / at rated input voltage 230 V / rated value	1 A
current limitation / of inrush current / at 25 °C / maximum	35 A
fuse protection type / at input	Fuse T 3.15A soldered
electrical data / output	
voltage curve / at output	Controlled, isolated DC voltage, adjustable from 48 V to 54 V
output voltage / at DC / rated value	54 V
display version / for normal operation	LED green for DC ok
behavior of the output voltage / when switching on	Overshoot of $U_a < 2\%$
startup delay time / maximum	1.5 s
voltage increase time / of the output voltage / maximum	15 ms
output current	
• rated value	1.6 A
• rated range	0 ... 1.8 A
supplied active power / typical	86 W
product feature / parallel switching of channels	No
number of parallel-switched equipment resources / for increasing the power	0
efficiency in percent	89 %
power loss [W]	11 W
electrical data / closed-loop control	
relative overall tolerance / of the voltage	1 %
residual ripple / maximum	0.05 V

voltage peak / maximum	0.2 V
relative control precision / of the output voltage <ul style="list-style-type: none"> on slow fluctuation of input voltage on slow fluctuation of ohm loading load step of resistive load 50/100/50 % / typical with rapid fluctuation of the input voltage by +/- 15% / typical 	0.2 % 0.5 % 0.5 % 0.3 %
setting time <ul style="list-style-type: none"> load step 50 to 100% / typical load step 100 to 50% / typical 	0.5 ms 0.5 ms
electrical data / protection and monitoring	
design of the overvoltage protection / at output	< 60 V
response value current limitation / typical	1.7 A
property of the output / short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
electrical data / safety	
galvanic isolation / between input and output	Yes
galvanic isolation	Safety extra-low output voltage U _{out} acc. to EN 60950-1
operating resource protection class	Class I
leakage current <ul style="list-style-type: none"> maximum typical 	3.5 mA 2 mA
interfaces	
number of electrical connections <ul style="list-style-type: none"> for power supply for signaling contact 	3 2
type of electrical connection <ul style="list-style-type: none"> for signaling contact at input at output 	Screw terminal 0.5 - 2.5 mm ² PE / L / N screw-type terminal 0.5 - 2.5 mm ² 2x + / 2x - , screw-type terminal 0.5 - 2.5 mm ²
signal inputs/outputs	
product component / signaling contact	Yes
relay design	Normal open contact (N/O)
operating voltage / of the signaling contacts <ul style="list-style-type: none"> at DC / rated value at DC / maximum 	24 V 60 V
operational current / of the signaling contacts <ul style="list-style-type: none"> at DC / maximum at DC / at 30 V / maximum 	0.3 A 0.3 A
design, dimensions and weights	
width	42 mm
height	125 mm
depth	125 mm
net weight	0.5 kg
product feature / of the enclosure / housing can be lined up	Yes
fastening method <ul style="list-style-type: none"> 19-inch installation wall mounting 35 mm top hat DIN rail mounting S7-300 rail mounting 	No No Yes No
ambient conditions	
ambient temperature <ul style="list-style-type: none"> during operation during storage during transport note 	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C Convection
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
environmental category / according to IEC 60721	Climate class 3K3, without condensation
protection class IP	IP20
standards, specifications, approvals	

standard	
<ul style="list-style-type: none"> • for safety / from CSA and UL • for emitted interference • for interference immunity 	cULus listed (UL508, CSA C22.2 No. 107.1) EN 61000-6-4: 2007 EN 61000-6-2
certificate of suitability	EN 61000-6-4: 2007
<ul style="list-style-type: none"> • CE marking • C-Tick 	Yes Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/snst http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	10/28/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK59230PS003AA2](#)