

product type designation

product description

MM991-2 (BFOC)

XR-300 media module

SCALANCE X accessory; Media module MM991-2; 2x 100 Mbit/s BFOC ports, optical; multimode optical up to max. 5 km.



interfaces

number of electrical/optical connections / for network components or terminal equipment / maximum	2
number of optical interfaces / for network components or terminal equipment / maximum	2
number of 100 Mbit/s ST(BFOC) ports / for multimode / integrated	2
design of the optical interface / for network components or terminal equipment	ST/BFOC
wavelength / of the optical interface	1310 nm; Multi-mode
connectable optical power relative to 1 mW	
• of the transmitter output / minimum	-19 dB
• of the transmitter output / maximum	-14 dB
• of the receiver input / maximum	-3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-32 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 5 km

ambient conditions

ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20

design, dimensions and weights

design	Media module
width	60 mm
height	22 mm
depth	100 mm
net weight	0.08 kg
fastening method	latched
• installation in media module slot	Yes

standards, specifications, approvals

standard	
• for FM	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3(2) G Ex nA [op is] IIC T4 DEKRA

• for safety / from CSA and UL • for hazardous zone / from CSA and UL • for emitted interference • for interference immunity	11 ATEX 0060 X UL 60950-1, CSA C22.2 No. 60950-1 UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4 EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes Yes Yes Ex nA IIC T4 Gc
Marine classification association • French marine classification society (BV)	Yes
MTBF	140 a
further information / internet links	
internet link • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	5/28/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK59912AB008AA0