

product description	XR-300 media module
	SCALANCE X accessory; Media module MM992-2LD; 2x 1000 Mbit/s SC-ports, optical; single-mode optical up to max. 10 km.



interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	2
number of optical interfaces / for network components or terminal equipment / maximum	2
number of 1000 Mbit/s SC ports (LX)	2
design of the optical interface / for network components or terminal equipment	SC
wavelength / of the optical interface	1310 nm; Single-mode
connectable optical power relative to 1 mW - of the transmitter output / minimum - of the transmitter output / maximum - of the receiver input / maximum	-9.5 dB -3 dB -3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-21 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 10 km
ambient conditions	
ambient temperature - during operation - during storage - during transport	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	Media module
width	60 mm
height	22 mm
depth	100 mm
net weight	0.08 kg
fastening method installation in media module slot	latched Yes
standards, specifications, approvals	
standard - for FM - for hazardous zone - for safety / from CSA and UL	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4 EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X UL 60950-1, CSA C22.2 No. 60950-1

• for hazardous zone / from CSA and UL • for emitted interference • for interference immunity	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4 EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes Yes Yes Ex nA IIC T4 Gc
Marine classification association • French marine classification society (BV)	Yes
MTBF	55 a
further information / internet links	
internet link • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

5/28/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK59922AM008AA0](#)