

product type designation

MM992-4LD

SCALANCE X accessory; Media module MM992-4LD; 4x 1000 Mbit/s SC-ports, optical; single-mode optical up to max. 10 km.



interfaces

number of electrical/optical connections / for network components or terminal equipment / maximum	4
number of optical interfaces / for network components or terminal equipment / maximum	4
number of 1000 Mbit/s SC ports (LX)	4
design of the optical interface / for network components or terminal equipment	SC
wavelength / of the optical interface	1310 nm; Single-mode
connectable optical power relative to 1 mW <ul style="list-style-type: none"> • of the transmitter output / minimum • of the transmitter output / maximum • of the receiver input / maximum 	-9.5 dB -3 dB -3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-21 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 10 km

ambient conditions


ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport 	0 ... 60 °C -40 ... +85 °C -40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20

design, dimensions and weights

design	Media module
width	120.3 mm
height	22.3 mm
depth	275.5 mm
net weight	0.3 kg
fastening method <ul style="list-style-type: none"> • installation in media module slot 	latched Yes

standards, specifications, approvals

standard <ul style="list-style-type: none"> • for safety / from CSA and UL • for emitted interference • for interference immunity 	UL 60950-1, CSA C22.2 No. 60950-2 EN 61000-6-4 (Class A) EN 61000-6-2
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007

<ul style="list-style-type: none"> • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking • E1 approval 	Yes Yes Yes Yes Ex nA IIC T4 Gc No
Marine classification association <ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
further information / internet links	
internet link <ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	5/28/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK59924AM008AA0](#)