

product type designation

product description

7/8 inch connecting cable

Plug-in cable (5-core), preferred length, preassembled with two 5-pole 7/8 inch male/female-contact connectors

7/8" plug-in cable for Power supply of the ET 200, pre-assembled cable with 2 7/8" connectors, 5-pole, 15 m.



suitability for use

Power supply of ET 200 modules with 7/8 inch power port to IP 65 degree of protection

cable designation

L-Y11Y-Z 5x1x1.5 GR

wire length

15 m

electrical data

insulation resistance coefficient

1 GΩ·m

operating voltage / RMS value

600 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

16 A

mechanical data

number of electrical cores

5

type of electrical connection

7/8 inch - 180

outer diameter

- of inner conductor
- of the wire insulation
- of cable sheath

1.55 mm
2.73 mm
10.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

design of stranding element

Pairs

conductor class

5

material

- of the conductor
- of the wire insulation
- of cable sheath

CU, blank
PVC
PUR

product component / PE connection

Yes

marking / of cores

Color, digits

color

- of the power line insulation
- of cable sheath

black
gray

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible
- with continuous bending

27 mm
63 mm
75 mm

number of bending cycles

5000000; For use in cable carriers, for 5 million bending cycles with a bending radius of 75 mm, an acceleration of 4 m/s² and a speed of 180 m/min

tensile load / maximum

500 N

weight per length

149 kg/km

plug

type of plug interlock

screwed

design of plug-in connection	7/8 inch - 180
connector coding	7/8 inch
ambient conditions	
ambient temperature	
• during operation	-40 ... +80 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
• during installation	-40 ... +80 °C
fire behavior	Flame-resistant acc. to IEC 60332-1
chemical resistance	
• to mineral oil	resistant
• to grease	resistant
radiological resistance / to UV radiation	resistant
protection class IP	IP65 / 67
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes
certificate of suitability	
• EAC approval	Yes
• RoHS conformity	Yes
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/20/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6XV18225BN15](#)