


product type designation

product description



PROFIBUS ECOFAST Hybrid Cable GP

ECOFAST Hybrid cable (data and energy wires), preferred length, assembled with ECOFAST connector and socket

PROFIBUS ECOFAST Hybrid Cable GP, 2xCu 0.64 mm, 4x Cu 1.5 mm², Cable pre-assembled with ECOFAST plug and socket, trailable, length 10 m.

suitability for use

Hybrid cable for connection of ECOFAST stations, UL approval

cable designation

02Y (ST)C 1x2x0.65/2.56 -150 LI LIY-Z Y 4x1x1.5 VI

wire length

10 m

electrical data

attenuation factor per length

• at 9.6 kHz / maximum	0.003 dB/m
• at 38.4 kHz / maximum	0.004 dB/m
• at 4 MHz / maximum	0.025 dB/m
• at 16 MHz / maximum	0.049 dB/m

impedance

• rated value	150 Ω
• at 9.6 kHz	270 Ω
• at 38.4 kHz	185 Ω
• at 3 MHz ... 20 MHz	150 Ω

relative symmetrical tolerance

• of the characteristic impedance at 9.6 kHz	10 %
• of the characteristic impedance at 38.4 kHz	10 %
• of the characteristic impedance at 3 MHz ... 20 MHz	10 %

loop resistance per length / maximum

138 Ω/km

shield resistance per length / maximum

15 Ω/km

insulation resistance coefficient

20 GΩ·m

operating voltage / maximum

80 V

capacity per length / at 1 kHz

30 pF/m

operating voltage / RMS value

600 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

12 A

mechanical data

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

number of electrical cores

6

type of electrical connection / FastConnect

No

outer diameter

• of inner conductor	0.67 mm
• of the wire insulation	2.56 mm
• of cable sheath	11 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

material

• of the wire insulation	polyethylene (PE)
--------------------------	-------------------

<ul style="list-style-type: none"> • of cable sheath 	PVC
color	
<ul style="list-style-type: none"> • of the insulation of data wires 	red / green
<ul style="list-style-type: none"> • of the power line insulation 	Black
<ul style="list-style-type: none"> • of cable sheath 	Violet
bending radius	
<ul style="list-style-type: none"> • with multiple bends / minimum permissible 	110 mm
number of bending cycles	1000000; For use in cable carriers, for 1 million bending cycles with a bending radius of 166 mm (15x D) and an acceleration of 4.0 m/s ²
tensile load / maximum	300 N
weight per length	154 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation 	-30 ... +80 °C
<ul style="list-style-type: none"> • during storage 	-30 ... +80 °C
<ul style="list-style-type: none"> • during transport 	-30 ... +80 °C
<ul style="list-style-type: none"> • during installation 	-30 ... +80 °C
<ul style="list-style-type: none"> • note 	Electrical properties measured at 20 Cel, verification according to DIN 47250 part 4 respectively DIN VDE 0490
fire behavior	flame-retardant according to IEC 60332-3-24 (Category C)
chemical resistance	
<ul style="list-style-type: none"> • to mineral oil 	Conditional resistance
<ul style="list-style-type: none"> • to grease 	Conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP65
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> • halogen-free 	Yes
<ul style="list-style-type: none"> • silicon-free 	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes; CM / CL3 / SunRes / OilRes
certificate of suitability	
<ul style="list-style-type: none"> • EAC approval 	Yes
<ul style="list-style-type: none"> • RoHS conformity 	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

5/21/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6XV18603PN10](#)