

### product type designation

product description

### PROFIBUS Cable 830-2

Plug-in cable comprising PROFIBUS standard cable, preferred length, preassembled with two 9-pole connectors

plug-in cable 830-2 for PROFIBUS, pre-assembled cable with two D-sub connectors 9-pole, Terminating resistors connectable, 3 m.



suitability for use

Cable for connecting PROFIBUS stations (e.g. HMI) to automation devices

cable designation

02YSY (ST) CY 1x2x0,64/2,55-150 VI KF 40 FR

wire length

3 m

### electrical data

number of electrical connections

2

attenuation factor per length

• at 9.6 kHz / maximum	0.0025 dB/m
• at 38.4 kHz / maximum	0.004 dB/m
• at 4 MHz / maximum	0.022 dB/m
• at 16 MHz / maximum	0.042 dB/m

operating voltage

• RMS value	80 V
-------------	------

### mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

outer diameter

• of inner conductor	0.65 mm
• of the wire insulation	2.55 mm
• of the inner sheath of the cable	5.4 mm

material

• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	PVC

color

• of the insulation of data wires	red/green
-----------------------------------	-----------

bending radius

• with single bend / minimum permissible	37.5 mm
• with multiple bends / minimum permissible	75 mm

weight per length

80 kg/km

### ambient conditions

ambient temperature

• note	Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
--------	--

fire behavior

flame resistant according to IEC 60332-3-24 (Category C) and UL 1685 (CSA FT 4)

chemical resistance

• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to water	conditional resistance

radiological resistance / to UV radiation	resistant
protection class IP	IP20
<b>standards, specifications, approvals</b>	
UL/ETL listing / 300 V Rating	Yes; c(UL)us, CMG / CL3 / Sun Res
UL/ETL style / 600 V Rating	Yes
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
• RoHS conformity	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
<b>further information / internet links</b>	
internet link	
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to website: Industrial communication	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Selection guide for cables and connectors	<a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**last modified:**

12/31/2021 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6XV18302AH30](#)