


product description



Standard bus cable (4 wires), preferred length, not assembled

IE FC TP Standard Cable GP 2x2 (PROFINET Type A), CAT5E, bus cable 4-wire, shielded, special configuration for quick assembly to IE FC RJ45 PLUG 2x2, 20 m.

suitability for use	Standard cable with rigid cores for fast installation
cable designation	2YY (ST) CY 2x2x0,64/1,5-100 GN SF/UTP
wire length	20 m
electrical data	
attenuation factor per length <ul style="list-style-type: none">at 10 MHz / maximumat 100 MHz / maximum	0.052 dB/m 0.195 dB/m
impedance <ul style="list-style-type: none">at 1 MHz ... 100 MHz	100 Ω
relative symmetrical tolerance <ul style="list-style-type: none">of the characteristic impedance at 1 MHz ... 100 MHz	15 %
near-end crosstalk per length <ul style="list-style-type: none">at 1 MHz ... 100 MHz	0.5 dB/m
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	115 mΩ/m
operating voltage <ul style="list-style-type: none">RMS value	80 V
NVP value in percent	69 %
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
type of electrical connection / FastConnect	Yes
core diameter <ul style="list-style-type: none">of AWG22 insulated conductor	0.64 mm
outer diameter <ul style="list-style-type: none">of inner conductorof the wire insulationof the inner sheath of the cableof cable sheath	0.64 mm 1.5 mm 3.9 mm 6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material <ul style="list-style-type: none">of the wire insulationof the inner sheath of the cableof cable sheath	polyethylene (PE) PVC PVC
color <ul style="list-style-type: none">of the insulation of data wiresof cable sheath	white/yellow/blue/orange green
bending radius	

<ul style="list-style-type: none"> • with single bend / minimum permissible 	19.5 mm
<ul style="list-style-type: none"> • with multiple bends / minimum permissible 	49 mm
tensile load / maximum	150 N
weight per length	61 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation 	-40 ... +75 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +75 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +75 °C
<ul style="list-style-type: none"> • during installation 	-40 ... +60 °C
<ul style="list-style-type: none"> • note 	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to IEC 60332-3-24 (Cat. C) and UL 1685 (CSA FT 4)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
<ul style="list-style-type: none"> • to mineral oil 	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
<ul style="list-style-type: none"> • to grease 	Conditional resistance
<ul style="list-style-type: none"> • to water 	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> • halogen-free 	No
<ul style="list-style-type: none"> • silicon-free 	Yes
wire length / for Industrial Ethernet	
<ul style="list-style-type: none"> • with 100BaseTX 	100 m
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us / CMG / (ETL)us PLTC/ ITC / Sun Res
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
<ul style="list-style-type: none"> • EAC approval 	Yes
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • RoHS conformity 	Yes
standard for structured cabling	Cat5e
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	No
<ul style="list-style-type: none"> • French marine classification society (BV) 	No
<ul style="list-style-type: none"> • Det Norske Veritas (DNV) 	No
<ul style="list-style-type: none"> • Germanische Lloyd (GL) 	No
<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) 	No
<ul style="list-style-type: none"> • Nippon Kaiji Kyokai (NK) 	No
<ul style="list-style-type: none"> • Polski Rejestr Statkow (PRS) 	No
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	WG
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	WGB
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
last modified:	7/19/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6XV18402AN20](#)