

product description



Standard bus cable (4 wires), preferred length, not assembled

Industrial Ethernet FC TP standard cable GP TP installation cable for Connection to IE FC RJ45 2x2, for universal use, CAT 5, 1000 m.

suitability for use	Standard cable with rigid cores for fast installation
cable designation	2YY (ST) CY 2x2x0,64/1,5-100 GN SF/UTP
wire length	1000 m
electrical data	
attenuation factor per length	
• at 10 MHz / maximum	0.052 dB/m
• at 100 MHz / maximum	0.195 dB/m
impedance	
• at 1 MHz ... 100 MHz	100 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	15 %
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	115 mΩ/m
operating voltage	
• RMS value	80 V
NVP value in percent	69 %
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
type of electrical connection / FastConnect	Yes
core diameter	
• of AWG22 insulated conductor	0.64 mm
outer diameter	
• of inner conductor	0.64 mm
• of the wire insulation	1.5 mm
• of the inner sheath of the cable	3.9 mm
• of cable sheath	6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	PVC
• of cable sheath	PVC
color	
• of the insulation of data wires	white/yellow/blue/orange
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	19.5 mm
• with multiple bends / minimum permissible	49 mm

tensile load / maximum	150 N
weight per length	61 kg/km
ambient conditions	
ambient temperature	
• during operation	-40 ... +75 °C
• during storage	-40 ... +75 °C
• during transport	-40 ... +75 °C
• during installation	-40 ... +60 °C
• note	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to IEC 60332-3-24 (Cat. C) and UL 1685 (CSA FT 4)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
wire length / for Industrial Ethernet	
• with 100BaseTX	100 m
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us / CMG / (ETL)us PLTC/ ITC / Sun Res
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
standard for structured cabling	Cat5e
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

7/19/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6XV18402AU10