


product type designation

product description

IE TP XP Cord 9/RJ45, 2x2

Crossover patch cable, preferred length, preassembled with one 9-pole D-sub connector and one RJ45 connector

Industrial Ethernet TP XP Cord 9/RJ45, TP cord pre-assembled with 1x RJ45 connector and 1x 9-pole ITP connector send and receive line crossed, length 10 m.



suitability for use

Easy connection of terminal devices to the IE FC cabling system

cable designation

LI 02YSCY 2x2x0,15/0,98 PIMF ICCS GN

wire length

10 m

electrical data

number of electrical connections

2

attenuation factor per length

• at 10 MHz / maximum	0.09 dB/m
• at 100 MHz / maximum	0.285 dB/m
• at 300 MHz / maximum	0.495 dB/m
• at 600 MHz / maximum	0.75 dB/m

impedance

• at 1 MHz ... 100 MHz	100 Ω
• at 10 MHz ... 600 MHz	100 Ω

relative symmetrical tolerance

• of the characteristic impedance at 1 MHz ... 100 MHz	15 %
• of the characteristic impedance at 10 MHz ... 600 MHz	6 %

transfer impedance per length / at 10 MHz

10 mΩ/m

loop resistance per length / maximum

300 mΩ/m

insulation resistance coefficient

150 GΩ·m

operating voltage

• RMS value	80 V
-------------	------

mechanical data

number of electrical cores

4

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

core diameter

• of AWG26 insulated conductor	0.48 mm
--------------------------------	---------

outer diameter

• of inner conductor	0.48 mm
• of the wire insulation	0.98 mm

width / of cable sheath

5.8 mm

symmetrical tolerance of width / of cable sheath

0.2 mm

thickness / of cable sheath

3.7 mm

symmetrical tolerance of thickness / of cable sheath

0.2 mm

material

• of the wire insulation	polyethylene (PE)
• of cable sheath	PVC

color

<ul style="list-style-type: none"> • of the insulation of data wires • of cable sheath 	white/blue, white/orange green
bending radius	
<ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible 	24 mm 42 mm
weight per length	32 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation 	-40 ... +70 °C -40 ... +70 °C -40 ... +70 °C -40 ... +70 °C
fire behavior	flame resistant according to DIN VDE 0472, part 804, test type B
chemical resistance	
<ul style="list-style-type: none"> • to mineral oil • to grease 	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> • halogen-free • silicon-free 	No Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	
<ul style="list-style-type: none"> • EAC approval • UL approval 	Yes Yes
standard for structured cabling	Cat5
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) 	No No No No No No No
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	WG WGB
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Selection guide for cables and connectors • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

1/14/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6XV18502MN10](#)