

### product type designation

product description

### IE Connecting Cable M12-90/M12-90

Flexible plug-in cable (4-wire), preferred length, prefabricated with two 4-pin M12 connectors (D-coded, 90° cable outlet)

IE Connecting Cable M12-90/M12-90, pre-assembled IE FC Trailing Cable GP, with 2 M12 connectors (D-coded) Length 10.0 m.



suitability for use

For connecting Industrial Ethernet stations (e.g. SIMATIC ET200 and SCALANCE XP-200) in IP 65/67 degree of protection

cable designation

2YY (ST) CY 2x2x0,75/1,5-100 LI GN

wire length

10 m

### electrical data

number of electrical connections

2

attenuation factor per length

- at 10 MHz / maximum
- at 100 MHz / maximum

0.063 dB/m  
0.213 dB/m

impedance

- at 1 MHz ... 100 MHz

100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz

5 %

near-end crosstalk per length

- at 1 MHz ... 100 MHz

0.5 dB/m

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

120 mΩ/m

operating voltage

- RMS value

80 V

NVP value in percent

66 %

### mechanical data

number of electrical cores

4

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

core diameter

- of AWG22 insulated conductor

0.75 mm

outer diameter

- of inner conductor
- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

0.75 mm  
1.5 mm  
3.9 mm  
6.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

polyethylene (PE)  
PVC  
PVC

color

- of the insulation of data wires

white/yellow/blue/orange

|  |   |
|--|---|
| • of cable sheath  | green   |
| bending radius   |   |
| • with single bend / minimum permissible                                 | 32.5 mm   |
| • with multiple bends / minimum permissible                              | 49 mm   |
| • with continuous bending  | 100 mm  |
| number of bending cycles   | 3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s <sup>2</sup> |
| tensile load / maximum   | 150 N   |
| weight per length  | 68 kg/km  |
| <b>plug</b>  |   |
| type of plug interlock   | screwed   |
| connector coding   |   |
| • of the M12 circular connector  | D-coded   |
| <b>ambient conditions</b>  |   |
| ambient temperature  |   |
| • during operation   | -25 ... +75 °C  |
| • during storage   | -25 ... +75 °C  |
| • during transport   | -25 ... +75 °C  |
| • during installation  | -10 ... +60 °C  |
| • note   | Electrical properties measured at 20 °C, tests according to DIN VDE 0472  |
| fire behavior  | flame resistant according to UL 1685 (CSA FT 4)   |
| chemical resistance  |   |
| • to mineral oil   | conditional resistance  |
| • to grease  | Conditional resistance  |
| radiological resistance / to UV radiation                                | resistant   |
| protection class IP  | IP65, IP67  |
| <b>product features, product functions, product components / general</b> |   |
| product feature  |   |
| • halogen-free   | No  |
| • silicon-free   | Yes   |
| <b>standards, specifications, approvals</b>                              |   |
| UL/ETL listing / 300 V Rating  | Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES   |
| UL/ETL style / 600 V Rating  | Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2  |
| certificate of suitability   |   |
| • EAC approval   | Yes   |
| • CE marking   | Yes   |
| • RoHS conformity  | Yes   |
| standard for structured cabling  | Cat5e   |
| Marine classification association  |   |
| • American Bureau of Shipping Europe Ltd. (ABS)                          | No  |
| • French marine classification society (BV)                              | No  |
| • Det Norske Veritas (DNV)   | No  |
| • Germanische Lloyd (GL)   | No  |
| • Lloyds Register of Shipping (LRS)                                      | No  |
| • Nippon Kaiji Kyokai (NK)   | No  |
| • Polski Rejestr Statkow (PRS)   | No  |
| reference code   |   |
| • according to IEC 81346-2   | WG  |
| • according to IEC 81346-2:2019  | WGB   |
| <b>further information / internet links</b>                              |   |
| internet link  |   |
| • to web page: selection aid TIA Selection Tool                          | <a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>   |
| • to website: Industrial communication                                   | <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>   |
| • to website: Industry Mall  | <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>   |
| • to website: Information and Download Center                            | <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>   |
| • to website: Selection guide for cables and connectors                  | <a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a>   |
| • to website: Image database   | <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>   |
| • to website: CAX-Download-Manager                                       | <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>   |
| • to website: Industry Online Support                                    | <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>   |

last modified:

2/3/2023 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6XV18708GN10