



Siemens Low Voltage Circuit Protection General Duty Safety Switches. 600A 2P 240V 3W FUSED GD TYPE 1

| General technical data                       |   |
|--|---|
| fastening method                             | SURFACE   |
| number of poles                              | 2   |
| suitability for operation                    | DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS |
| Electricity                                  |   |
| ampacity                                     | 600 A   |
| Environmental conditions                     |   |
| ambient temperature during operation maximum | 85 °C   |
| ambient temperature during operation minimum | -29 °C  |
| Model  |   |
| product brand name                           | SIEMENS   |
| product sub brand name                       | VBII  |
| product type designation                     | GENERAL DUTY SWITCH                             |
| type of electrical connection                | MECHANICAL LUGS                                 |
| Mechanical Design                            |   |
| design of the actuating element              | SINGLE THROW                                    |
| material                                     | STEEL   |
| General product approval                     |   |
| certificate of suitability                   | UL98  |

last modified:

9/15/2021 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

GF226NA