



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches - Type ENCLOSED / SAFETY SWITCH Meets stds: UL. Built material: 304SSsingle throw action. Rated 600VDC (200A) at 60Hz.3-Pole. Insulated. TYPE 3R enclosure with 2 or 3 point mounting. No special features listed.

General technical data	
mechanical service life (operating cycles) typical	8000
fastening method	SURFACE
number of poles	3
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	200 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
special product feature	PHOTOVOLTAIC RATED
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the housing	TYPE 3R
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/15/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[HF364RPV](#)