




Electrically held lighting contactor, Contactor amp rating 60A, 0 N.C. / 6 N.O.  
Poles, 480VAC 60HZ coil, 1 NO / 1 NC auxiliary contacts Non-combination type,  
(no disconnect device), Enclosure NEMA type 12, Dust/drip proof for indoors

|   |   |
|---|---|
| product brand name  | Class LE                                      |
| design of the product   | Electrically held lighting contactor          |
| special product feature   | Compact design; Finger safe control terminals |
| <b>General technical data</b>   |   |
| weight [lb]   | 35 lb   |
| Height x Width x Depth [in]   | 16 × 13 × 6 in                                |
| touch protection against electrical shock                               | NA for enclosed products                      |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                                       |
| ambient temperature [°F]  |   |
| • during storage  | -67 ... +176 °F                               |
| • during operation  | 32 ... 104 °F                                 |
| ambient temperature   |   |
| • during storage  | -55 ... +80 °C                                |
| • during operation  | 0 ... 40 °C                                   |
| country of origin   | Germany                                       |
| <b>Contactors</b>   |   |
| size of contactor   | 60 Amp  |
| number of NO contacts for main contacts                                 | 6   |
| number of NC contacts for main contacts                                 | 0   |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V   |
| mechanical service life (operating cycles) of the main contacts typical | 10000000                                      |
| contact rating of the main contacts of lighting contactor               |   |
| • with electronic ballast [LED driver] (1 pole per 1 phase) rated value | 16A @120V / 8A @277V 1p 1ph                   |
| • at tungsten (1 pole per 1 phase) rated value                          | 60A @277V 1p 1ph                              |
| • at tungsten (2 poles per 1 phase) rated value                         | 60A @480V 2p 1ph                              |
| • at tungsten (3 poles per 3 phases) rated value                        | 60A @480V 3p 3ph                              |
| • at ballast (1 pole per 1 phase) rated value                           | 60A @347V 1p 1ph                              |
| • at ballast (2 poles per 1 phase) rated value                          | 60A @600V 2p 1ph                              |
| • at ballast (3 poles per 3 phases) rated value                         | 60A @600V 3p 3ph                              |
| • at resistive load (1 pole per 1 phase) rated value                    | 60A @347V 1p 1ph                              |
| • at resistive load (2 poles per 1 phase) rated value                   | 60A @600V 2p 1ph                              |
| • at resistive load (3 poles per 3 phases) rated value                  | 60A @600V 3p 3ph                              |
| <b>Auxiliary contact</b>  |   |
| number of NC contacts at contactor for auxiliary contacts               | 2   |
| number of NO contacts at contactor for auxiliary contacts               | 2   |
| number of total auxiliary contacts maximum                              | 14  |
| contact rating of auxiliary contacts of contactor according to UL       | A600 / P600                                   |
| <b>Coil</b>   |   |

|   |   |
|---|---|
| type of voltage of the control supply voltage   | AC                                      |
| control supply voltage  |   |
| • at DC rated value   | 0 ... 0 V                               |
| • at AC at 50 Hz rated value  | 0 ... 0 V                               |
| • at AC at 60 Hz rated value  | 480 ... 480 V                           |
| apparent pick-up power of magnet coil at AC   | 376 VA                                  |
| apparent holding power of magnet coil at AC   | 33 VA                                   |
| operating range factor control supply voltage rated value of magnet coil  | 0.85 ... 1.1                            |
| ON-delay time   | 80 ms                                   |
| OFF-delay time  | 10 ... 18 ms                            |
| <b>Enclosure</b>  |   |
| degree of protection NEMA rating of the enclosure   | NEMA 12 enclosure                       |
| design of the housing   | dustproof and drip-proof for indoor use |
| <b>Mounting/wiring</b>  |   |
| mounting position   | Vertical                                |
| fastening method  | Surface mounting and installation       |
| type of electrical connection for supply voltage line-side  | Screw-type terminals                    |
| tightening torque [lbf-in] for supply   | 26 ... 39 lbf-in                        |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded   | 2x (18 ... 2 AWG), 1x (18 ... 1 AWG)    |
| temperature of the conductor for supply maximum permissible   | 75 °C                                   |
| material of the conductor for supply  | CU                                      |
| type of electrical connection for load-side outgoing feeder   | Screw-type terminals                    |
| tightening torque [lbf-in] for load-side outgoing feeder  | 26 ... 39 lbf-in                        |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded  | 2x (18 ... 2 AWG), 1x (18 ... 1 AWG)    |
| temperature of the conductor for load-side outgoing feeder maximum permissible  | 75 °C                                   |
| material of the conductor for load-side outgoing feeder   | CU                                      |
| type of electrical connection of magnet coil  | Screw-type terminals                    |
| tightening torque [lbf-in] at magnet coil   | 7 ... 10 lbf-in                         |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded   | 2x (20 ... 16 AWG), 2x (18 ... 14 AWG)  |
| temperature of the conductor at magnet coil maximum permissible   | 75 °C                                   |
| material of the conductor at magnet coil  | CU                                      |
| type of electrical connection at contactor for auxiliary contacts   | Screw-type terminals                    |
| tightening torque [lbf-in] at contactor for auxiliary contacts  | 7 ... 10 lbf-in                         |
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded  | 2x (20 ... 16 AWG), 2x (18 ... 14 AWG)  |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible  | 75 °C                                   |
| material of the conductor at contactor for auxiliary contacts   | CU                                      |
| <b>Short-circuit current rating</b>   |   |
| design of the fuse link for short-circuit protection of the main circuit required   | 100kA@600V (Class J 80A max)            |
| design of the short-circuit trip  | Thermal magnetic circuit breaker        |
| maximum short-circuit current breaking capacity (I <sub>cu</sub> )  |   |
| • at 240 V  | 24 kA                                   |
| • at 480 V  | 65 kA                                   |
| • at 600 V  | 25 kA                                   |
| certificate of suitability  | NEMA ICS 2; UL 508A                     |
| <b>Further information</b>  |   |
| Industrial Controls - Product Overview (Catalogs, Brochures,...)  |   |
| <a href="http://www.usa.siemens.com/iccatalog">www.usa.siemens.com/iccatalog</a>  |   |
| Industry Mall (Online ordering system)  |   |
| <a href="https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:LEN02D006480C">https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:LEN02D006480C</a>         |   |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  |   |
| <a href="https://support.industry.siemens.com/cs/US/en/ps/US2:LEN02D006480C">https://support.industry.siemens.com/cs/US/en/ps/US2:LEN02D006480C</a>   |   |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)   |   |
| <a href="http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:LEN02D006480C&amp;lang=en">http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:LEN02D006480C&amp;lang=en</a> |   |
| Certificates/approvals  |   |
| <a href="https://support.industry.siemens.com/cs/US/en/ps/US2:LEN02D006480C/certificate">https://support.industry.siemens.com/cs/US/en/ps/US2:LEN02D006480C/certificate</a>                   |   |



last modified:

7/12/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[LEN02D006480C](#)