

Datasheet

mSATA

3TE7 series

- mSATA SATA III solution for industrial field
- High IOPS
- iSMART disk health monitoring
- iPower Guard for protecting unstable start up and shut down.
- iData Guard for abnormal power failure




Introduction


Innodisk mSATA 3TE7 is SATA III 6.0 Gb/s flash based disk, which adopts latest SATA III NAND controller with Innodisk's exclusive L³ FW architecture. The upgraded L³ FW architecture, combining Innodisk signature 4K mapping algorithm L² FW architecture with powerful LDPC technology, makes 3TE7 series have outstanding high IOPS, better data integrity and extended lifespan through reducing the bad block number happening. Built-in thermal sensor and iData Guard ensure data integrity and reliability of mSATA 3TE7 for industrial applications.

mSATA SSD 3TE7 series

Diagram For 32GB~512GB



For 1TB~2TB



Contact us for more information about the mSATA 3TE7.

Innodisk is a service-driven provider of industrial embedded flash and DRAM storage products and technologies, with a focus on the industrial/embedded, aerospace and defense, and cloud computing industries.

Specifications

Interface	SATA III
Flash Type	3D TLC
Capacity	32GB~2TB
Max. Channels	4
Sequential R/W (MB/sec, max.)*	560 / 520 MB/s
4KB Random (QD32) R/W (IOPS)*	83,000/75,000
Max. Power Consumption	2W
Thermal Sensor	√
External DRAM Buffer	-
H/W Write Protect	Optional
ATA Security	√
S.M.A.R.T.	√
Dimension (WxLxH)	29.85 X 50.8 X 3.7 mm
Environment	Vibration: 20G @ 7~2000Hz Shock: 1500G @ 0.5ms Storage Temperature: -40°C ~ +85°C MTBF: 3 million hours
* Performance based on CrystalDiskMark 6.0.2 with file size 1000MB	

Ordering Information (Please refer to TPS for detail)

Operation Temp.	32GB	64GB	128GB	256GB	512GB	1TB	2TB
Standard Grade (0°C ~ +70°C)	DEMSR-32GDK1EC1SL	DEMSR-64GDK1% C1SL	DEMSR-A28DK1% C1DL	DEMSR-B56DK1% C1QL	DEMSR-C12DK1% C*QL	DEMSR-01TDK1GCAQL	DEMSR-02TDK1GCAQQ
Wide-Temp. Grade (-20°C ~ +85°C)	NA	DEMSR-64GDK1GW1SL	DEMSR-A28DK1GW1DL	DEMSR-B56DK1GW1QL	DEMSR-C12DK1GW1QL	DEMSR-01TDK1GWAQL	DEMSR-02TDK1GWAQQ

%. E: 64 layers 3D TLC; G: 96 layers 3D TLC

*. PCB version control

innodisk

www.innodisk.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Innodisk:

[DEMSR-01TDK1GWAQL](#) [DEMSR-01TDK1KCAQL](#) [DEMSR-02TDK1GWAQQ](#) [DEMSR-02TDK1KCAQL](#) [DEMSR-64GDK1GW1SL](#) [DEMSR-64GDK1KCASL](#) [DEMSR-A28DK1GW1DL](#) [DEMSR-A28DK1KCADL](#) [DEMSR-B56DK1GW1QL](#) [DEMSR-B56DK1KCAQL](#) [DEMSR-C12DK1GW1QL](#) [DEMSR-C12DK1KCAQL](#)