

**EOL - Modlink MSDD-set: Frame 4000-68123-0000000,**

discontinued - End of Life Date: 2024-12-31

Art.No.: 4000-68123-0230010

Weight: 0.771

Country of origin: CN

Model designation: X MSDD\_2MV\_VDE MIT LED\_

[Link to Product](#)**Illustration**



Product may differ from Image



| Commercial data                               |                       |
|-----------------------------------------------|-----------------------|
| ECLASS-6.0                                    | 27189217              |
| ECLASS-6.1                                    | 27189217              |
| ECLASS-7.0                                    | 27189217              |
| ECLASS-8.0                                    | 27189217              |
| ECLASS-9.0                                    | 27182806              |
| ECLASS-10.1                                   | 27182806              |
| ECLASS-11.1                                   | 27182806              |
| ECLASS-12.0                                   | 27182806              |
| ETIM-5.0                                      | EC002625              |
| ETIM-6.0                                      | EC002625              |
| ETIM-7.0                                      | EC002625              |
| ETIM-8.0                                      | EC002625              |
| customs tariff number                         | 85366990              |
| customs tariff number                         | 85366990              |
| customs tariff number                         | 85366990              |
| EAN                                           | 4048879034418         |
| EAN                                           | 4048879034418         |
| EAN                                           | 4048879034418         |
| Packaging unit                                | 1                     |
| Packaging unit                                | 1                     |
| Packaging unit                                | 1                     |
| Frame                                         |                       |
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Material housing                              | Fine zinc die casting |
| Coating housing                               | surface finished      |
| Germany (VDE)                                 |                       |

|                               |                    |
|-------------------------------|--------------------|
| Connection cross section max. | 6 mm <sup>2</sup>  |
| AWG number max.               | 10                 |
| Operating voltage AC          | 250 V              |
| Operating current             | 16 A               |
| Status indication LED         | yellow             |
| Connection                    | Screw terminals SK |
| No. of poles                  | 2 + PE             |
| Connections per pole          | 2                  |
| Protection contact present    | yes                |

#### SUB-D9

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Operating current                     | 3 A                                            |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | SUB-D9                                         |
| Family type Back side                 | SUB-D9                                         |
| Gender                                | female                                         |
| Gender Rear                           | Solder connection                              |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 9                                              |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-68123-0230010](#)