

Miro 6,2 Timer On-delay max.3-300 sec.**MIRO 6.2 TIMER ON-DELAY**

Art.No.: 52301

Weight: 0.035

Country of origin: CZ




Model designation: Miro on-delay Zeitrelais max.3-300 sec.



Relay output

Switch on delay: 3...300 s

Screw terminals

safe separation (EN 60947-1)

[Link to Product](#)**Illustration**



Product may differ from Image



Header

Material short text

Miro on-delay Zeitrelais max.3-300 sec.

Commercial data

URL Webshop	https://shop.murrelektronik.com/52301
GTIN	4048879026994
ECLASS-6.0	27210990
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-7.1	27371790
ECLASS-8.0	27371605
ECLASS-8.1	27371605
ECLASS-9.0	27371605
ECLASS-9.1	27371605
ECLASS-10.0.1	27371605
ECLASS-10.1	27371605
ECLASS-11.0	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ECLASS-13.0	27371605
ECLASS-14.0	27371605
ETIM-5.0	EC001439
ETIM-6.0	EC001439
ETIM-7.0	EC001439
ETIM-8.0	EC001439
customs tariff number	85364900
EAN	4048879026994
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	204 V
Input voltage DC max.	264 V
Input current	20 mA
Input current DC max.	16 mA

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-08-15

Control voltage DC	24 V
Control voltage DC min.	204 V
Control voltage DC max.	264 V

Electrical data | Output

Output voltage adjustable	no
Output current max.	6 A
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1,500 VA
Power rating DC max.	120 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 Cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 Cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	15 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Height	91 mm
Width	62 mm
Depth	71 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C

Connection type 5

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	16
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	15
Family construction form	terminal

No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	18
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	+ A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	- A 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[52301](#)