

M12 male 0° A-cod. IDC




4-pol., 0.25 - 0.5mm², 4 - 5,1mm

Art.No.: 7000-12481-0000000
Weight: 0.02
Country of origin: DE
Model designation: MSAL0-AC-T-IDC

Male straight
M12, 4-pole
IDC terminals
Connection cross section: 0.25...0.5 mm²
Art.No. 7005 - M12 Lite - (plastic hexagonal screw) on request
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Side 1

| | |
|-------------------------------------|------|
| Family construction form | M12 |
| Degree of protection (EN IEC 60529) | IP67 |

Commercial data

| | |
|------------|----------|
| ECLASS-6.0 | 27279221 |
| ECLASS-6.1 | 27260702 |

| | |
|-----------------------|---------------|
| ECLASS-7.0 | 27440102 |
| ECLASS-8.0 | 27440102 |
| ECLASS-9.0 | 27440116 |
| ECLASS-10.1 | 27440102 |
| ECLASS-11.1 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ETIM-5.0 | EC002635 |
| customs tariff number | 85366990 |
| GTIN | 4048879201841 |
| Packaging unit | 1 |

Electrical data | Supply

| | |
|------------------------------------|------|
| Operating voltage AC max. | 32 V |
| Operating voltage DC max. | 32 V |
| Current operating per contact max. | 4 A |

Installation

| | |
|-------------------------------|----------------------|
| Connection cross section min. | 0,25 mm ² |
| Connection cross section max. | 0,5 mm ² |
| Single wire diameter min. | 0,1 mm |

Installation | Connection

| | |
|-------------------------------|--------|
| Wire insulation diameter min. | 1,2 mm |
| Wire insulation diameter max. | 1,6 mm |
| Tightening torque | 0,6 Nm |

Device protection | Electrical

| | |
|--|------------------|
| Additional condition protection degree | screwed, mounted |
| Rated surge voltage | 0,8 kV |
| Material group (IEC 60664-1) | III |

Mechanical data | Mounting data

| | |
|---------------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
| Clamping range min. | 4 mm |
| Clamping range max. | 5,1 mm |
| Height | 55 mm |
| Width | 15 mm |
| Depth | 15 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -25 °C |
| Operating temperature max. | 85 °C |

Important installation notes

| | |
|------------------------|---|
| Note on strain relief | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties. |
| Note on bending radius | Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[7000-12481-0000000](#)